

# Rittal – The System.

Faster – better – everywhere.



## DK 7010.220

## Senzorji

State: 3.6.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7010.220 - Senzorji for CMC III, PDU, LCP, IoT interface

The leak sensor monitors the base for conductive liquids (leakage) using a 15-metre long sensor cable.

## Features

|                              |  |
|------------------------------|--|
| Št. Modela                   | DK 7010.220  |
| Zasnova                      | Leak sensor, for bayed enclosure suites  |
| Prednosti                    | Hitra povezava in samodejno zaznavanje s funkcijo plug & play<br>Napajanje se omogoči s povezavo z vmesnikom CAN-BUS.  |
| Aplikacije                   | Nadzor ohišij v IT, industriji in upravljanju objektov<br>Nadzor ohišij, prostorov in zabojnikov v IT okolju   |
| Način delovanja              | Settings can be made via the CMC III processing unit, PDU or IoT interface<br>15-metrski kabel senzorja je pritrjen na podnožje.<br>Če kabel senzorja pride v stik s prevodno tekočino, bo senzor sporočil alarm za puščanje |
| Material                     | Plastika   |
| Površinska obdelava          | Spredaj: gladko<br>Ohišje: teksturirano  |
| Barva                        | RAL 9005   |
| Obseg dobave                 | Senzor puščanja<br>Detektorski kabel, 15 m<br>Montažna plošča<br>Sestavni deli   |
| Povezava s CAN vodilom       | Direct   |
| Vmesniki                     | 2 x RJ45 CAN bus   |
| Mere                         | Širina: 110 mm<br>Višina: 30 mm<br>Globina: 40 mm  |
| Delovno temperaturno območje | 0 °C...45 °C   |

## Features

---

|                                      |   |
|--------------------------------------|---|
| Vlažnost okolice (brez kondenzacije) | 5...95 %  |
| Paketi                               | 1 pc(s).  |
| Neto teža                            | 0,85 kg   |
| Bruto teža                           | 1,057 kg  |
| Carinska tarifna številka            | 90261029  |
| ETIM 9                               | EC002627  |
| Opis izdelka                         | DK Leak point sensor, for bayed enclosure suites, connection via CAN bus interface, WxHxD: 110x30x40 mm, RAL 9005 |

## Approvals

---

|              |                           |
|--------------|---------------------------|
| Approvals    | UL + C-UL (listed)        |
| Explanations | Declaration of conformity |