

Rittal – The System.

Faster – better – everywhere.



SE 5842.500

Sistem samostojećih ohišij SE 8

State: 21.6.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SE 5842.500 - Sistem samostojećih ohišij SE 8

Individual sheet steel enclosure with stable enclosure body, two integrated mounting levels, screw-fastened rear panel and door. Roof and sides from a single piece with roll-formed frame. Fully compatible interior installation with the TS 8, enabling full integration into the TS 8 product family. Enclosure widths ranging from 600 to 1800 mm Time-saving assembly work due to the roll-formed side panels



Features

| | |
|---------------------|---|
| Št. Modela | SE 5842.500 |
| Material | Ohišje: jeklena pločevina 1,5 mm Vrata: jeklena pločevina, 2,0 mm Zadnja plošča: jeklena pločevina, 1,5 mm Plošče z uvodnicami: jeklena pločevina, 1,5 mm Montažna plošča: jeklena pločevina, 3,0 mm |
| Površinska obdelava | Ohišje, vrata in zadnja plošča: temeljni premaz, prašno barvna zunanost, teksturirana barva Montažna plošča in plošče z uvodnicami: pocinkano |
| Barva | RAL 7035 |
| Obseg dobave | Ohišje, zaprt zgornji del in stranice Vrata Zapiranje vrat pri enokrilih ohišjih, možnost zamenjave na nasprotno stran Montažna plošča Kabelske uvodnice Zadnja plošča, snemljiva Ključavnica: 3 mm dvojna ključavnica 2 luknjani tirnici TS 18 x 38 mm Zadnja plošča, dvodelna |

Features

| | |
|------------------------------|--|
| Mere | Širina: 1.600 mm Višina: 1.800 mm Globina: 400 mm |
| Mere montažne plošče (Š x V) | 1.499 mm x 1.696 mm |
| Razred zaščite po IEC 60 529 | IP 55 |
| Razred zaščite NEMA | NEMA 12 NEMA 3R |
| IK koda | IK10 |
| Število vrat | 2 |
| Osnovni material | Sheet steel |
| Paketi | 1 pc(s). |
| Neto teža | 222 kg |
| Bruto teža | 231,5 kg |
| Carinska tarifna številka | 94032080 |
| ECLASS 8.0 | 27180101 |
| Opis izdelka | SE Free-standing enclosure system, WHD: 1600x1800x400 mm, Sheet steel, with mounting plate, two doors at the front |

Approvals

| | |
|--------------|---|
| Approvals | UL + C-UL (listed) |
| Explanations | Declaration of conformity Declaration of conformity UK |