


**Rittal – The System.**

Faster – better – everywhere.



**VX 8640.023**

**Vogalni element podnožja/  
podstavka z obrobami podnožja/  
podstavka, spredaj in zadaj, 200  
mm**



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES



FRIEDHELM LOH GROUP

# VX 8640.023 - Vogalni element podnožja/podstavka z obrobami podnožja/podstavka, spredaj in zadaj, 200 mm za VX, VX IT, VX SE, TE, TS, TS IT, TP, PC, IW

Heavy-duty base/plinth corner pieces with moulded self-positioning to the enclosure, may be used with or without trim panels depending on the application. Large openings in the base/plinth corner piece for optimum access to the screw-fastening point, may be concealed with a plastic corner and baying cover.

## Features

|                        |  |
|------------------------|--|
| Št. Modela             | VX 8640.023  |
| Material               | Podnožje/vogalni kos podnožja: jeklena pločevina<br>Obrobe podnožja/podstavka: jeklena pločevina<br>Kotni in povezovalni pokrov: plastika  |
| Barva                  | RAL 9005   |
| Obseg dobave           | 4 vogalni elementi podnožja/podstavka, višina 200 mm<br>4 vogalni pokrovi<br>1 povezovalni pokrov<br>1 obroba podnožja/podstavka, spredaj/zadaj, višina 200 mm<br>2 obrobi podnožja/podstavka, spredaj/zadaj, višina 100 mm<br>Sestavni deli |
| Opomba                 | Stranske obrobe podnožja/podstavka zaokrožujejo podnožje/<br>podstavek ali zagotavljajo dodatno stabilizacijo med podnožjem/<br>podstavkom oziroma omogočajo notranjo konfiguracijo podnožja/<br>podstavka                                   |
| Mere                   | Višina: 200 mm   |
| Primerno za            | Širina: = 800 mm   |
| Tipska ocena po UL 50E | Type 1<br>Type 12  |
| Teža/pakiranje         | 9,24 kg  |
| Paketi                 | 2 pc(s).   |
| Neto teža              | 7,52 kg  |

# Features

---

|                           |   |
|---------------------------|---|
| Bruto teža                | 9,24 kg   |
| Carinska tarifna številka | 94039910  |
| ETIM 9                    | EC000721  |
| ETIM 8                    | EC000721  |
| ECLASS 8.0                | 27182003  |
| Opis izdelka              | VX Base/plinth corner piece, with base/plinth trim panel, front and rear, H: 200 mm, for W: 800 mm, sheet steel |

# Approvals

---

|           |                  |
|-----------|------------------|
| Approvals | UL + C-UL - FTTA |
|-----------|------------------|