


**Rittal – The System.**

Faster – better – everywhere.



**SZ 2482.710**

**Predĺženie rozhrania s napojením na stenu**

State: 23.5.2026 (Source: [rittal.com/sk-sk](http://rittal.com/sk-sk))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SZ 2482.710 - Predĺženie rozhrania s napojením na stenu

For extending the internal enclosure interfaces – e.g. from industrial PCs and switches – up to the outside of the enclosure.

## Features

|                                         |                                                                                                                                                                                  |
|-----------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Obj. č.                                 | SZ 2482.710                                                                                                                                                                      |
| Prevedenie                              | RJ45 pripojenie na stenu - zásuvka / vnútorné pripojenie - konektor                                                                                                              |
| Výhody                                  | Rýchly prístup pri údržbe<br>Zostáva zachovaný stupeň krytia skrine<br>Kontramatica sa sama zareže do náteru, takže vznikne vodivý spoj<br>Ochranné viečko zaistené proti strate |
| Materiál                                | Skriňa: mosadz<br>Kryt: hliník<br>Tesnenie: polyamid                                                                                                                             |
| Povrch                                  | Skriňa: poniklovaná<br>Kryt: eloxovaný                                                                                                                                           |
| Dĺžka                                   | 1 m                                                                                                                                                                              |
| Rozmery                                 | Dĺžka: 1 m                                                                                                                                                                       |
| Na hrúbku steny (max.)                  | 1 - 6 mm                                                                                                                                                                         |
| Stupeň krytia IP podľa normy IEC 60 529 | IP67 with sealed protective cap                                                                                                                                                  |
| Balenie                                 | 1 pc(s).                                                                                                                                                                         |
| Netto hmotnosť                          | 0,079 kg                                                                                                                                                                         |
| Brutto hmotnosť                         | 0,096 kg                                                                                                                                                                         |
| Číslo colnej sadzby                     | 85444290                                                                                                                                                                         |
| ETIM 9                                  | EC001408                                                                                                                                                                         |
| ETIM 8                                  | EC001408                                                                                                                                                                         |
| ECLASS 8.0                              | 19059205                                                                                                                                                                         |
| Popis výrobku                           | Predĺženie rozhrania SZ, s pripojením na stenu, RJ45, D: 1000 mm                                                                                                                 |