


Rittal – The System.

Faster – better – everywhere.



KX 1577.000

E-box KX, ocel'ový plech

State: 2.6.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



KX 1577.000 - E-box KX, ocelový plech

The small enclosure KX, E-Box KX (sheet steel), offers remarkable ease of assembly and flexibility when selecting lock systems.



Features

| | |
|--|---|
| Obj. č. | KX 1577.000 |
| Materiál | Skriňa: ocelový plech Dvere: ocelový plech, po obvode polyuretánové penové tesnenie |
| Povrch | Skriňa a dvere: základná farba nanosená máčaním, z vonkajšej strany štruktúrovaná prášková farba Montážna doska: pozinkovaná |
| Farba | RAL 7035 |
| Rozsah dodávky | Skriňa s dverami Montážna doska Otočný uzáver s uzatváracou vložkou Doppelbart 3 mm Pánty 180° |
| Protection category NEMA | NEMA 1 NEMA 3R NEMA 4 NEMA 12 |
| Stupeň krytia IP podľa normy EN 60 529 | IP 66 |

Features

| | |
|----------------------------------|--|
| Type rating podľa UL 50E | Type 1 Type 3R Type 4 Type 12 |
| Kód IK | IK08 |
| Rozmery | Šírka: 300 mm Výška: 400 mm Hĺbka: 155 mm |
| Rozmery montážnej dosky (Š x V) | 275 mm x 385 mm |
| Hrúbka materiálu skrine | 1,25 mm |
| Hrúbka materiálu dverí | 1,25 mm |
| Hrúbka materiálu montážnej dosky | 2 mm |
| Uzáver | Počet uzáverov: 1 |
| Základný materiál | Sheet steel |
| Balenie | 1 pc(s). |
| Netto hmotnosť | 6,86 kg |
| Brutto hmotnosť | 6,98 kg |
| PCF per pack (cradle-to-gate) | 40,18 kg CO2 eq (Cat B) |
| Note on PCF category | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Číslo colnej sadzby | 84879059 |
| ETIM 9 | EC000261 |
| ETIM 8 | EC000261 |
| ECLASS 8.0 | 27180101 |
| Popis výrobku | KX E-Box, ŠxVxH: 300x400x155, oceľový plech, s montážnou doskou, s dverami. |

Approvals

Approvals

Approvals

Bureau Veritas
DNV
Lloyds Register
UL + C-UL (listed)

Certificates

Protection category

Explanations

Manufacturer's declaration
Declaration of conformity
Declaration of conformity UK
PCF-declaration