

Rittal – The System.

Faster – better – everywhere.



PC 4650.100

Skrine pre počítačové systémy

State: 1.6.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



PC 4650.100 - Skrine pre počítačové systémy Nerezová oceľ

PC enclosure systems based on VX SE made from stainless steel 1.4301 (AISI 304). Identical design principle as the sheet steel PC. Practical rear door allows easy access for servicing. High level of access protection thanks to moulded side panels and roof, plus interior glazed door lock and lockable keyboard drawer.



Features

Obj. č.	PC 4650.100
Prevedenie	Nerezová oceľ
Materiál	Skriňa: nerezová oceľ 1.4301 (AISI 304), 1,5 mm Dvere na zadnej strane: nerezová oceľ 1.4301 (AISI 304), 2,0 mm Podlahové plechy: nerezová oceľ 1.4301 (AISI 304), 1,5 mm Pole monitora: jednovrstvové bezpečnostné sklo, 4 mm
Povrch	Jemne zbrúsený povrch, zrnitosť 400
Rozsah dodávky	Skriňa hore a po stranách uzavretá Dvere vzadu s tyčovým uzáverom Presklené dvere hore, blokovací uzáver z vnútornej strany Prístrojová polica Zásuvná priehradka na klávesnicu s výklopným čelom pre opierku dlane a podložku pod myš Uzatváracia vložka, zámok č. 3524 E Dvere dole s tyčovým uzáverom Podlahové plechy, delené

Features

Rozmery	Šírka: 600 mm Výška: 1.600 mm Hĺbka: 630 mm
Stupeň krytia IP podľa normy IEC 60 529	IP 55
Stupeň krytia NEMA	NEMA 12
Základný materiál	Stainless steel 1.4301 (AISI 304)
Balenie	1 pc(s).
Netto hmotnosť	115 kg
Brutto hmotnosť	120,5 kg
Číslo colnej sadzby	94032080
ETIM 9	EC002502
ETIM 8	EC002502
ECLASS 8.0	27180501
Popis výrobku	PC PC enclosure system, WHD: 600x1600x630 mm, Stainless steel 1.4301, with keyboard drawer

Approvals

Approvals	UL + C-UL (listed)
Certificates	Surface finish
Explanations	Manufacturer's declaration Declaration of conformity Declaration of conformity UK