


Rittal – The System.

Faster – better – everywhere.



TS 4695.000

Montážna výstuha

State: 10.7.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 4695.000 - Montážna výstuha pre VX, TS, VX SE, TP, AX

For simple attachment of cable ducts, cable conduit holders, contact hazard protection cover plates, equipment installed on the door, cable clamping and attachment.



Features

Obj. č.	TS 4695.000
Technické údaje	Dierovanie Ø 4,5 mm v rozmerovom rastri 25 mm
Materiál	Oceľový plech
Povrch	Pozinkovaný
Rozsah dodávky	Vrátane upevňovacieho materiálu
Dĺžka	440 mm
Možnosti montáže VX	Do hĺbky skrine 500 mm
Možnosti montáže VX SE	Do hĺbky skrine 500 mm, na vonkajšej montážnej rovine
Možnosti montáže AX	Do šírky dverí 500 mm, s otočným uzáverom Do šírky dverí 500 mm, s 3-bodovým uzamykacím systémom, dvere s pántami
Možnosti inštalácie AX z nehrdzavejúcej ocele	V šírke dverí 500 mm, v dverách s pántami, v spojení s dierovanou lištou dverí
Možnosti montáže TS	V skrini šírky/hĺbky 500 mm, na vonkajšej montážnej rovine
Možnosti montáže AE	V skrini šírky/výšky 500 mm, v spojení s lištou pre vnútornú montáž AE
Možnosti montáže TP	V podstavci pultu TP a kompaktného pultu, hĺbka rozvádzača 500 mm, v spojení s lištou pre vnútornú montáž pre TP, kompaktná rozvádzacia skriňa HD

Features

Vhodné pre	Typ skrine: VX TS VX SE TP AX AE Šírka/hĺbka: 500 mm
Balenie	20 pc(s).
Netto hmotnosť	4,4 kg
Brutto hmotnosť	4,603 kg
PCF per pack (cradle-to-gate)	21 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Číslo colnej sadzby	73269098
ETIM 9	EC002620
ETIM 8	EC002620
ECLASS 8.0	27189261
Popis výrobku	TS montážna lišta, pre VX, TS, VX SE, TP, pre vonkajšiu montážnu rovinu: pre š/h: 500 mm, D: 440 mm

Approvals

Explanations	PCF-declaration
--------------	-----------------