

# Rittal – The System.

Faster – better – everywhere.



## PC 5366.300

# Skrine pre počítačové systémy

State: 20.6.2026 (Source: [rittal.com/sk-sk](http://rittal.com/sk-sk))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# PC 5366.300 - Skrine pre počítačové systémy

Secure accommodation of all PC components, from monitors, to PCs, to keyboards. For ultimate ease of operation in a modern design. Perfect protection from humidity and dirt, temperature fluctuations and unauthorised access.

## Features

Obj. č.	PC 5366.300
Prevedenie	s presklenými dverami hore, zásuvkou pre klávesnicu, malým montážnym poľom a prístrojovou policou
Materiál	Skriňa, dvere, zadné dvere, montážne pole, odkladacie priehradky: oceľový plech Rukoväte, dekoratívne kryty: plast Zakrytie dverí: hliník Sklenené okno: jednovrstvové bezpečnostné sklo
Povrch	Skriňa a dvere: základná farba nanosená máčaním, z vonkajšej strany štruktúrovaná prášková farba Montážne pole, odkladacia priehradka: práškovaný povrch
Farba	Skriňa, dvere, dekoračné kryty, odkladacie priehradky: RAL 7035 Rukoväť: v odtieni podobnom RAL 9006 Pole monitora, stredový diel dverí: RAL 7015
Rozsah dodávky	Skriňa, dvere, zadné dvere Presklené dvere, horné Montážne pole, malé Zásuvná priehradka pre klávesnicu Prístrojová polica
Rozmery	Šírka: 600 mm Výška: 1.600 mm Hĺbka: 636 mm
Stupeň krytia IP podľa normy IEC 60 529	IP 55
Stupeň krytia NEMA	NEMA 12
Max. rozmer klávesnice (Š x V x H)	480 x 70 x 260 mm
Základný materiál	Sheet steel

# Features

---

Balenie	1 pc(s).
Netto hmotnosť	93,5 kg
Brutto hmotnosť	95,5 kg
Číslo colnej sadzby	94032080
ECLASS 8.0	27180501
Popis výrobku	PC PC enclosure system, WHD: 600x1600x636 mm, Sheet steel, with glazed door at the top, keyboard drawer, component shelf, small mounting compartment, component shelf

# Approvals

---

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK