


Rittal – The System.

Faster – better – everywhere.



VX 8228.000

System radových skříň VX25

State: 7.7.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 8228.000 - Systém radových skříň VX25 Základná skriňa

The standard in enclosure manufacturing: Enclosure frame with one or two front doors, rear panel, mounting plate, roof plate, divided gland plates. Perfectly suited to efficient enclosure interior installation.



Features

Obj. č.	VX 8228.000
Materiál	Rámová konštrukcia skrine: oceľový plech, 1,5 mm Strecha: oceľový plech 1,5 mm Dvere: oceľový plech, 2,0 mm Zadná stena: oceľový plech, 1,5 mm Podlahové plechy: oceľový plech 1,5 mm Montážna doska: oceľový plech, 3,0 mm
Povrch	Rámová konštrukcia skrine: základná farba nanosená máčaním Dvere, strecha a zadná stena: základná farba nanosená máčaním, z vonkajšej strany štruktúrovaná prášková farba Montážna doska a podlahové plechy: pozinkované
Farba	RAL 7035

Features

Rozsah dodávky	Rámová konštrukcia skrine Dvere Pánty dverí vpravo, je možné zameniť na ľavú stranu Strešný plech Zadná stena Podlahové plechy Montážna doska 2 montážne lišty 18 x 39 mm Uzáver: Doppelbart, 3 mm
Rozmery	Šírka: 1.200 mm Výška: 2.200 mm Hĺbka: 800 mm
Rozmery montážnej dosky (Š x V)	1.099 mm x 2.096 mm
Stupeň krytia IP podľa normy EN 60 529	IP 55
Stupeň krytia NEMA	NEMA 12
Type rating podľa UL 50E	Type 1 Type 12
Kód IK	IK10
Počet dverí	2
Základný materiál	Sheet steel
Balenie	1 pc(s).
Netto hmotnosť	193 kg
Brutto hmotnosť	210 kg
PCF per pack (cradle-to-gate)	554,92 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Číslo colnej sadzby	94032080
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101

Features

Popis výrobku

Systém radovo spojených skříň VX, ŠxVxH: 1200x2200x800 mm,
oceľový plech, s montážnou doskou, 2 dvere vpredu

Approvals

Approvals

UL + C-UL (listed)

Certificates

Surface finish

Explanations

Manufacturer's declaration
Declaration of conformity
PCF-declaration