

# Rittal – The System.

Faster – better – everywhere.



## TS 4694.000 Montážna výstuha

State: 22.5.2026 (Source: [rittal.com/sk-sk](http://rittal.com/sk-sk))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# TS 4694.000 - Montážna výstuha pre VX, TS, VX SE, TP, AX

For simple attachment of cable ducts, cable conduit holders, contact hazard protection cover plates, equipment installed on the door, cable clamping and attachment.



## Features

Obj. č.	TS 4694.000
Technické údaje	Dierovanie Ø 4,5 mm v rozmerovom rastrí 25 mm
Materiál	Oceľový plech
Povrch	Pozinkovaný
Rozsah dodávky	Vrátane upevňovacieho materiálu
Dĺžka	340 mm
Možnosti montáže VX	V skrini šírky/hĺbky 500 mm, na vonkajšej montážnej rovine
Možnosti montáže VX SE	V skrini šírky/hĺbky 500 mm, na vonkajšej montážnej rovine
Možnosti montáže AX	Do šírky dverí 400 mm, s otočným uzáverom
Možnosti montáže TS	V skrini šírky/hĺbky 500 mm, na vonkajšej montážnej rovine
Možnosti montáže TP	V podstavci pultu TP a kompaktného pultu, hĺbka rozvádzača 400 mm, v spojení s lištou pre vnútornú montáž pre TP, kompaktná rozvádzacia skriňa HD
VX base/plinth installation options	In base/plinth width/depth 400 mm on the base/plinth trim panels, in conjunction with base/plinth installation bracket

# Features

---

Vhodné pre	Typ skrine: VX TS VX SE TP AX Šírka/hĺbka: 400 mm
Vhodné pre	Systém podstavca VX
Balenie	20 pc(s).
Netto hmotnosť	3,2 kg
Brutto hmotnosť	3,52 kg
PCF per pack (cradle-to-gate)	16,36 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Číslo colnej sadzby	73269098
ETIM 9	EC002620
ETIM 8	EC002620
ECLASS 8.0	27189261
Popis výrobku	TS montážna lišta, pre VX, TS, VX SE, TP, pre vonkajšiu montážnu rovinu: pre š/h: 400 mm, d: 340 mm

# Approvals

---

Explanations	PCF-declaration
--------------	-----------------