

Rittal – The System.

Faster – better – everywhere.



TS 4697.000

Montážna výstuha

State: 11.7.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 4697.000 - Montážna výstuha pre VX, TS, VX SE, TP, AX

For simple attachment of cable ducts, cable conduit holders, contact hazard protection cover plates, equipment installed on the door, cable clamping and attachment.



Features

Obj. č.	TS 4697.000
Technické údaje	Dierovanie Ø 4,5 mm v rozmerovom rastri 25 mm
Materiál	Oceľový plech
Povrch	Pozinkovaný
Rozsah dodávky	Vrátane upevňovacieho materiálu
Dĺžka	740 mm
Možnosti montáže VX	V skrini šírky/hĺbky 800 mm
Možnosti montáže VX SE	V skrini šírky/hĺbky 800 mm
Možnosti montáže AX	Do šírky dverí 800 mm, s otočným uzáverom
Možnosti inštalácie AX z nehrdzavejúcej ocele	V šírke dverí 800 mm, s otočným uzáverom, v spojení s dierovanou lištou dverí
Možnosti montáže PC	Do šírky skrine 800 mm, na vonkajšej montážnej rovine
Možnosti montáže TS	V skrini šírky/hĺbky 800 mm, na vonkajšej montážnej rovine
Možnosti montáže AE	V skrini šírky/výšky 800 mm, v spojení s lištou pre vnútornú montáž AE
VX base/plinth installation options	In base/plinth width/depth 800 mm on the base/plinth trim panels, in conjunction with base/plinth installation bracket

Features

Vhodné pre	Typ skrine: VX TS VX SE PC AX AE Šírka/hĺbka: 800 mm
Vhodné pre	System podstavca VX
Balenie	20 pc(s).
Netto hmotnosť	7,7 kg
Brutto hmotnosť	7,817 kg
PCF per pack (cradle-to-gate)	34,91 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Číslo colnej sadzby	73269098
ETIM 9	EC002620
ETIM 8	EC002620
ECLASS 8.0	27189261
Popis výrobku	TS montážna lišta, pre VX, TS, VX SE, TP, pre vonkajšiu montážnu rovinu: pre B/B, D: 800 mm, D: 740 mm

Approvals

Explanations	PCF-declaration
--------------	-----------------