



# Rittal – The System.

Faster – better – everywhere.



## VX 8660.006

# Rohové diely podstavca s krytom podstavca vpredu a vzadu

State: 23.5.2026 (Source: [rittal.com/sk-sk](http://rittal.com/sk-sk))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# VX 8660.006 - Rohové diely podstavca s krytom podstavca vpredu a vzadu pre systém podstavca VX, oceľový plech

Base/plinth corner pieces with trim panels for flexible cable entry.



## Features

|                |                                                                                                                                                                                           |
|----------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Obj. č.        | VX 8660.006                                                                                                                                                                               |
| Výhody         | Spoločiteľný - veľmi vysoká stabilita podstavca<br>Flexibilné – mnoho možností montáže v interiéri s VX príslušenstvom<br>Jednoduché – zakončenie v jednej rovine medzi bodmi zoradovania |
| Materiál       | Rohový diel podstavca: oceľový plech<br>Kryt podstavca vpredu/vzadu: oceľový plech<br>Rohový a radový kryt: plast                                                                         |
| Farba          | RAL 9005                                                                                                                                                                                  |
| Rozsah dodávky | 4 rohové kryty<br>Vrátane upevňovacieho materiálu<br>4 rohové diely podstavca, výška 100 mm<br>2 kryty podstavca vpredu/vzadu, výška 100 mm                                               |
| Poznámka       | Bočnice podstavca, na zakončenie jednotky podstavca, pre prídavnú vzájomnú stabilizáciu podstavcov alebo pre vnútorné vybavenie podstavcov                                                |
| Rozmery        | Výška: 100 mm                                                                                                                                                                             |

# Features

|                               |                                                                                                                |
|-------------------------------|----------------------------------------------------------------------------------------------------------------|
| Vhodné pre                    | Typ skrine: VX<br>VX IT<br>VX SE<br>TX CableNet<br>TS<br>TS IT<br>TP<br>PC<br>IW<br>CX<br>Šírka: = 1.100 mm    |
| Type rating podľa UL 50E      | Type 1<br>Type 12                                                                                              |
| Hmotnosť/balenie              | 6,6 kg                                                                                                         |
| Balenie                       | 2 pc(s).                                                                                                       |
| Netto hmotnosť                | 6,4 kg                                                                                                         |
| Brutto hmotnosť               | 6,6 kg                                                                                                         |
| PCF per pack (cradle-to-gate) | 23 kg CO2 eq (Cat B)                                                                                           |
| Note on PCF category          | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Číslo colnej sadzby           | 94039910                                                                                                       |
| ETIM 9                        | EC000721                                                                                                       |
| ETIM 8                        | EC000721                                                                                                       |
| ECLASS 8.0                    | 27182003                                                                                                       |
| Popis výrobku                 | Rohové diely podstavca s krytom VX, vpredu a vzadu, V: 100 mm, pre Š: 1100 mm, oceľový plech                   |

# Approvals

|              |                  |
|--------------|------------------|
| Approvals    | UL + C-UL - FTTA |
| Explanations | PCF-declaration  |