

# Rittal – The System.

Faster – better – everywhere.



## VX 8828.000

# System radových skříň VX25

State: 30.5.2026 (Source: [rittal.com/sk-sk](http://rittal.com/sk-sk))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# VX 8828.000 - Systém radových skříň VX25 Základná skriňa

The standard in enclosure manufacturing: Enclosure frame with one or two front doors, rear panel, mounting plate, roof plate, divided gland plates. Perfectly suited to efficient enclosure interior installation.



## Features

Obj. č.	VX 8828.000
Materiál	Rámová konštrukcia skrine: ocelový plech, 1,5 mm Strecha: ocelový plech 1,5 mm Dvere: ocelový plech, 2,0 mm Zadná stena: ocelový plech, 1,5 mm Podlahové plechy: ocelový plech 1,5 mm Montážna doska: ocelový plech, 3,0 mm
Povrch	Rámová konštrukcia skrine: základná farba nanosená máčaním Dvere, strecha a zadná stena: základná farba nanosená máčaním, z vonkajšej strany štruktúrovaná prášková farba Montážna doska a podlahové plechy: pozinkované
Farba	RAL 7035

# Features

Rozsah dodávky	Rámová konštrukcia skrine Dvere Pánty dverí vpravo, je možné zameniť na ľavú stranu Strešný plech Zadná stena Podlahové plechy Montážna doska 2 montážne lišty 18 x 39 mm Uzáver: Doppelbart, 3 mm
Rozmery	Šírka: 800 mm Výška: 2.200 mm Hĺbka: 800 mm
Rozmery montážnej dosky (Š x V)	699 mm x 2.096 mm
Stupeň krytia IP podľa normy EN 60 529	IP 55
Stupeň krytia NEMA	NEMA 12
Type rating podľa UL 50E	Type 1 Type 12
Kód IK	IK10
Počet dverí	1
Základný materiál	Sheet steel
Balenie	1 pc(s).
Netto hmotnosť	135,4 kg
Brutto hmotnosť	146,8 kg
PCF per pack (cradle-to-gate)	391,14 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Číslo colnej sadzby	94032080
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101

# Features

---

Popis výrobku

Systém radovo spojených skříň VX, ŠxVxH: 800x2200x800 mm, ocelový plech, s montážnou doskou, jednodverová, dvere vpředu

# Approvals

---

Approvals

UL + C-UL (listed)

Certificates

Surface finish

Explanations

Manufacturer's declaration  
Declaration of conformity  
Declaration of conformity UK  
PCF-declaration