

# Rittal – The System.

Faster – better – everywhere.



## TS 4596.000 Support strip

State: 07.04.2026 (Source: [rittal.com/ua-en](http://rittal.com/ua-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# TS 4596.000 - Support strip for VX, TS, VX SE, TP, AX

For simple attachment of cable ducts, cable conduit holders, contact hazard protection cover plates, equipment installed on the door, cable clamping and attachment.



## Features

|   |   |
|---|---|
| Model No.                               | TS 4596.000   |
| Product description                     | For simple attachment of cable ducts, cable conduit holders, contact hazard protection cover plates, equipment installed on the door, cable clamping and attachment.                    |
| Technical specifications                | 4.5 mm diameter hole on a 25 mm pitch pattern   |
| Material                                | Sheet steel   |
| Surface finish                          | Zinc-plated   |
| Supply includes                         | Assembly parts  |
| Length                                  | 490 mm  |
| To fit door width                       | 600 mm  |
| VX installation options                 | In door width 600 mm  |
| VX SE installation options              | In door width 600 mm<br>In enclosure width/depth 500 mm, on the inner mounting level  |
| AX installation options                 | In door width 600 mm, with 3-point lock system, in the lockable door<br>In enclosure width 500 mm and in enclosure height 600 mm, in conjunction with rail for interior installation AX |
| AX stainless steel installation options | In enclosure width 500 mm<br>In enclosure height 600 mm   |
| Installation options, AX plastic        | In door width 600 mm  |

# Features

|  |   |
|--|---|
| Installation options for 3-part AX                           | In the enclosure depth 673 mm or in the width of the wall section   |
| PC installation options                                      | In door width 600 mm  |
| WI installation options                                      | In door width 600 mm  |
| TS installation options                                      | In door width 600 mm<br>In enclosure width/depth 500 mm, on the inner mounting level  |
| Installation options for VX base/<br>plinth, stainless steel | In base/plinth depth 600 mm, in conjunction with M6 multi-tooth<br>screws and M6 nuts   |
| To fit   | Enclosure type: VX<br>TS<br>VX SE<br>PC<br>IW<br>AX<br>AX plastic<br>AX wall-mounted enclosure, 3-part<br>Width/depth: 500 mm |
| To fit   | VX base/plinth system, stainless steel  |
| Packs of   | 20 pc(s).   |
| Net weight   | 4.06 kg   |
| Gross weight   | 5.1 kg  |
| PCF per pack (cradle-to-gate)                                | 19.2 kg CO2 eq (Cat B)  |
| Note on PCF category   | Category B: PCF value (cradle-to-gate) based on the product weight,<br>approximately calculated and self-declared             |
| Customs tariff number  | 73269098  |
| ETIM 9   | EC002620  |
| ETIM 8   | EC002620  |
| ECLASS 8.0   | 27189261  |
| Product description  | TS Support strip, for TS, VX SE, TP, for inner mounting level: for W/D:<br>500 mm, for door width: 600 mm, L: 490 mm          |

# Approvals

---

Explanations

PCF-declaration