

Rittal – The System.

Faster – better – everywhere.



CP 6212.065

Support section, height-adjustable

State: 02.04.2026 (Source: rittal.com/ua-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



CP 6212.065 - Support section, height-adjustable for support arm systems

The new height-adjustable support section ensures that you always have a good view of the key parameters in human/machine interaction. The system can be fitted directly to the components in the CP 120 support arm system without any further adaptation on the wall side, and on the enclosure side on support arm system CP 60.



Features

| | |
|---------------------|--|
| Model No. | CP 6212.065 |
| Product description | The new height-adjustable support section ensures that you always have a good view of the key parameters in human/machine interaction. The system can be fitted directly to the components in the CP 120 support arm system without any further adaptation on the wall side, and on the enclosure side on support arm system CP 60 or CP 120 depending on the model. |
| Benefits | <ul style="list-style-type: none">Support arm holds securely in any positionPrecise coordination to the suspended load via an adjusting screw at the front of the support sectionAdjusting screw can be accessed without dismantling any componentsLarge cable tray and cable cable routing at the rotation points for safetyRemovable cover for simple cable entryTilting angle of the mounted enclosure is identical in every height positionCables with connectors such as DVI, VGA are easily insertedBroad weight range from 4 to 60 kg with three systems. (Weight range applies to configured enclosure and vertical support section.) |

Features

| | |
|-----------------------------------|--|
| Technical specifications | Cable tray: 36 x 11 mm (W x H), max. connector gland: 41 x 17 mm (W x H) More ergonomic with an adjustment range of 990 mm (± 495 mm) |
| Applications | For tall and short operators For seated and standing work |
| Material | Joint parts: Cast aluminium Concertina section: Plastic |
| General colour | RAL 7035 |
| Colour | RAL 7035 |
| Supply includes | Assembly parts |
| Length | 1,100 mm |
| Connection options enclosure | CP 60 |
| Connection options wall / machine | CP 120 |
| Note | In combination with support support section, height adjustable observe: When using an intermediate hinge, the height-adjustable support section should always be inserted in the closest horizontal position to the enclosure. |
| Dimensions | Length: 1,100 mm |
| Load capacity | 4 kg...15 kg |
| Note on Model No. | Maximum cross-section for cable entry 41 x 17 mm Weight range applies to configured enclosure and vertical support section. |
| Packs of | 1 pc(s). |
| Net weight | 15.2 kg |
| Gross weight | 16 kg |
| Customs tariff number | 73269098 |
| ETIM 9 | EC000882 |
| ECLASS 8.0 | 27400556 |
| Product description | CP support section, height-adjustable, for CP 120/60, length 1050 mm |