

# Rittal – The System.

Faster – better – everywhere.



## CX 6703.000

## CX pedestal

State: 24.08.2025 (Source: [rittal.com/ua-en](http://rittal.com/ua-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# CX 6703.000 - CX pedestal

CX pedestals, four widths and two different depths provide the basis for every console solution. The AX lock plate ensures a uniform appearance, and two-part gland plates are included with the supply for simple cable routing.



## Features

|                 |   |
|-----------------|---|
| Model No.       | CX 6703.000   |
| Design          | Pedestal  |
| Material        | Enclosure: Sheet steel 1.5 mm<br>Door: Sheet steel, 2.0 mm, all-round foamed-in PU seal<br>Mounting plate: Sheet steel, 2.5 mm                |
| Surface finish  | Enclosure and door: Dipcoat primed, powder-coated on the outside, textured paint<br>Mounting plate: Zinc-plated                               |
| Colour          | RAL 7035  |
| Supply includes | Enclosure open at top<br>Door or double-door at front, with 3-point locking system<br>Mounting plate<br>Gland plates<br>Lock: 3 mm double-bit |
| Dimensions      | Width: 1,600 mm<br>Height: 675 mm<br>Depth: 400 mm  |

# Features

|                                     |  |
|-------------------------------------|--|
| Dimensions mounting plate (W x H)   | 1,520 mm x 625 mm  |
| Number of doors                     | 2  |
| Door opening angle                  | 130°   |
| IK Code                             | IK10   |
| Note                                | <p>A cover plate is required to seal the pedestal</p> <p>A desk unit and desk unit cover plate are required for 2-part console assembly</p> <p>A desk unit and console are required for 3-part console assembly.</p> |
| IP protection category to IEC 60529 | IP 55  |
| Protection category NEMA            | <p>NEMA 1</p> <p>NEMA 12</p>   |
| Basic material                      | Sheet steel  |
| Number of locks                     | 1  |
| Lock version                        | 3-point lock system  |
| Lock insert                         | 3 mm double-bit  |
| Lock                                | <p>Lock version: 3-point lock system</p> <p>Number of locks: 1</p> <p>Lock insert: 3 mm double-bit</p>   |
| Packs of                            | 1 pc(s).   |
| Net weight                          | 75   |
| Gross weight                        | 76.5   |
| Customs tariff number               | 94032080   |
| EAN                                 | 4028177983779  |
| ETIM 9                              | EC000784   |
| ETIM 8                              | EC000784   |
| ECLASS 8.0                          | 27180504   |

# Approvals

|              |                           |
|--------------|---------------------------|
| Approvals    | UL + C-UL (listed)        |
| Explanations | Declaration of conformity |