

# Rittal – The System.

Faster – better – everywhere.



## SV 9670.005

## Baying systems TS 8

State: 02.08.2025 (Source: [rittal.com/ua-en](http://rittal.com/ua-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9670.005 - Baying systems TS 8 Fuse-switch-disconnector enclosure

Baying systems TS 8 for the distribution of electrical power with fused fuse-switch disconnectors from Jean Müller or ABB.

## Features

|                                      |                                                                                                                                                                                                                                      |
|--------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Model No.                            | SV 9670.005                                                                                                                                                                                                                          |
| Material                             | Sheet steel                                                                                                                                                                                                                          |
| Surface finish                       | Enclosure frame: Dipcoat-primed<br>Door(s), roof, rear panel: Dipcoat-primed, powder-coated on the outside, textured paint<br>Gland plates: Zinc-plated                                                                              |
| Colour                               | RAL 7035                                                                                                                                                                                                                             |
| Supply includes                      | Enclosure frame with r/h door hinge, left side open<br>Roof<br>Rear panel<br>Three-piece gland plates<br>Lock: 3 mm double-bit<br>4 eyebolts<br>Locating frame for disconnectors with fuses (brands ABB SlimLine/ Jean Müller SASIL) |
| Test specification                   | IEC 61 439-1/-2<br>IEC 61 641                                                                                                                                                                                                        |
| IP protection category to IEC 60 529 | Up to IP 3X, depending on the panels                                                                                                                                                                                                 |
| Dimensions                           | Width: 1,000 mm<br>Height: 2,000 mm<br>Depth: 600 mm                                                                                                                                                                                 |
| Packs of                             | 1 pc(s).                                                                                                                                                                                                                             |
| Net weight                           | 122.1                                                                                                                                                                                                                                |
| Gross weight                         | 133.4                                                                                                                                                                                                                                |

# Features

|            |               |
|------------|---------------|
| EAN        | 4028177814547 |
| ETIM 9     | EC002525      |
| ECLASS 8.0 | 27180101      |

# Approvals

|              |                                                           |
|--------------|-----------------------------------------------------------|
| Explanations | Declaration of conformity<br>Declaration of conformity UK |
|--------------|-----------------------------------------------------------|