

# Rittal – The System.

Faster – better – everywhere.



## HD 4000.064

## Printer enclosure HD

State: 23/08/2025 (Source: [rittal.com/uae-en](https://www.rittal.com/uae-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# HD 4000.064 - Printer enclosure HD

Hygienically designed enclosure for siting printers and other PC components in the production hall

## Features

|                                   |                                                                                                                                                                                                                                                |
|-----------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Model No.                         | HD 4000.064                                                                                                                                                                                                                                    |
| Benefits                          | For hygienic, secure siting of printers in the production hall<br>Combinable with HD command panel to assemble a complete PC enclosure<br>Pull-out, height-adjustable component shelf for fast access to printer, e.g. for changing the labels |
| Material                          | Enclosure and door: Stainless steel 1.4301 (AISI 304)<br>Lock insert HD: Stainless steel 1.4404 (AISI 316L)<br>Seal: Silicone, compliant with FDA Guideline 21 CFR 177.2600<br>Component shelf: Sheet steel, spray-finished                    |
| Surface finish                    | Enclosure and door: Brushed, grain 400, peak-to-valley height < 0.8 µm<br>Seal: Blue, dyed (RAL 5010)                                                                                                                                          |
| Supply includes                   | Enclosure of all-round solid construction<br>Door with inserted seal<br>Door hinged on the right, may be swapped to the left<br>Component shelf                                                                                                |
| Options                           | Without side rails<br>Without component shelf<br>With mounting plate<br>HD supporting structure with levelling                                                                                                                                 |
| Dimensions                        | Width: 810 mm<br>Height, front: 863 mm<br>Height rear: 888 mm<br>Depth: 496 mm                                                                                                                                                                 |
| Material thickness - enclosure    | 1.5 mm                                                                                                                                                                                                                                         |
| Material thickness - door         | 2 mm                                                                                                                                                                                                                                           |
| Protection category to IEC 60 529 | IP 66                                                                                                                                                                                                                                          |

# Features

|                       |               |
|-----------------------|---------------|
| Packs of              | 1 pc(s).      |
| Net weight            | 54.2          |
| Gross weight          | 54.2          |
| Customs tariff number | 94032080      |
| EAN                   | 4028177709522 |
| ETIM 9                | EC000261      |
| ETIM 8                | EC000261      |
| ECLASS 8.0            | 27180101      |