

Rittal – The System.

Faster – better – everywhere.



AS 4051.131

Wire Station WS 540

State: 16/08/2025 (Source: [rittal.com/uae-en](https://www.rittal.com/uae-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4051.131 - Wire Station WS 540

Mobile wiring workstation, height-adjustable, for flexible use in the workshop. For ergonomic, fatigue-free wire processing work.

Features

| | |
|---------------------|--|
| Model No. | AS 4051.131 |
| Design | Processing edition |
| Product description | Mobile wiring workstation, height-adjustable, for flexible use in the workshop. For ergonomic, fatigue-free wire processing work. |
| Benefits | <p>Electronically adjustable desk for the optimum working height, adjustable from 710 – 1250 mm</p> <p>Multiplex worktop, washable and scratch-resistant</p> <p>Ideal solution in conjunction with the length-cutting and crimping machines plus pre-assembled wires with the Wire Terminal</p> <p>Integral scale for quick manual measurements</p> <p>Prepared to accommodate a monitor for wire processing with Eplan Smart Wiring</p> <p>Optionally expandable with shelves for wire boxes, wire reels and holders for tools and small parts</p> <p>For flexible use in the workshop thanks to rubberised wheels</p> <p>Drawer with shadow board prepared for tools</p> |

Features

| | |
|-----------------------|---|
| Supply includes | Wiring table with electrical height adjuster Connection cable, 7 m 7-way socket strip, with rocker switch 1 Wire Station WS 540 1 component support, left 1 component support, right 1 LED work light 2 mounting struts, vertical 2 adaptor brackets 1 waste bin 4 wire pack holders, left 4 wire pack holders, right 1 wire coil holder, left 1 wire coil holder, right 1 wire guide strut, vertical 1 wire guide component support |
| Assembly instruction | The vertical mounting struts, Model No. 4051.106, are required for accessories such as storage box holders, magazine supports etc. |
| Input voltage | 230 V AC, 50 Hz |
| Working height | Working height (min.): 710 mm Working height (max.): 1,205 mm |
| Height adjustable y/n | Yes |
| Applications | For machining wires with Rittal length-cutting and crimping machines |
| Packs of | 1 pc(s). |
| Net weight | 160 |
| Gross weight | 220.3 |
| Customs tariff number | 94032080 |
| EAN | 4028177963658 |
| ETIM 8 | EC002778 |
| ECLASS 8.0 | 21100208 |

Approvals

Explanations

Declaration of conformity