

Rittal – The System.

Faster – better – everywhere.



VX 5302.036

Brush kit

State: 23/05/2026 (Source: rittal.com/uae-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 5302.036 - Brush kit for cable duct VX IT

Cut-outs for cable routing at any given positions in the side panel, rear panel, doors, roof and gland plate may be finished off attractively by simply attaching the brush strip.

Features

Model No.	VX 5302.036
Product description	For all-round shielding of the 482.6 mm (19") mounting level and targeted routing of the cold air flow to the installed equipment.
Benefits	Simple assembly with tool-free quick-release fastening Alternatively suitable for screw-fastening Tailored to the maximum enclosure height 47 U for cutting to the required individual length
Applications	The brush kit is designed for combining two vertical cable ducts on both sides of the 482.6 mm (19") mounting level. The brush kit may be combined with a cable duct and used as an alternative to the air baffle plate. A combination with air baffle plate and cable duct is also possible as partial installation
Function principle	The brush kit consists of vertical brush strips for the area between the cable duct and side panel as well as horizontal air baffle plates with brush strips for sealing in the roof and floor area on the 482.6 mm (19") mounting level
Material	Brush strip: Plastic, UL 94-V0 Bristles: Plastic, UL 94-HB Air baffle plates: Sheet steel, spray finished
Colour	RAL 9005
Supply includes	2 vertical brush strips, both sides 2 horizontal air baffle plates, top and bottom 2 horizontal brush strips, top and bottom between the first 482.6 mm (19") mounting level and the roof or gland plate 8 brush strips between the cable duct and roof/base plate Assembly parts
Bristle length	48 mm

Features

Installation options	482.6 mm (19") mounting angles, standard in the VX IT Dynamic 482.6 mm (19") mounting angles in the VX IT
Assembly instruction	When using the cable duct combined with the brush kit as an air routing component, the cable entry openings in the cable duct must be closed or covered with a cable management panel with brush strip
To fit	Width: = 800 mm
Packs of	1 pc(s).
Net weight	4.6 kg
Gross weight	4.8 kg
Customs tariff number	39259020
ETIM 9	EC012298
ECLASS 8.0	27142421
Product description	Brush kit for VX IT cable duct, for all-round shielding of the 19" mounting level and targeted routing of the cold air flow to the installed equipment. Bristle length 48 mm, enclosure width 800 mm