


**Rittal – The System.**

Faster – better – everywhere.



**VX 8619.720**

**Punched section with mounting  
flange, 14 x 39 mm**

State: 07/05/2026 (Source: [rittal.com/uae-en](http://rittal.com/uae-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# VX 8619.720 - Punched section with mounting flange, 14 x 39 mm for VX, VX SE, PC, IW, AX

For securing cable ducts, cable conduit holders, equipment installed on the door, etc.



## Features

|   |   |
|---|---|
| Model No.                               | VX 8619.720   |
| Product description                     | For attaching cable ducts, cable conduit holders, equipment installed on the door, etc.   |
| Material                                | Sheet steel   |
| Surface finish                          | Zinc-plated   |
| Supply includes                         | Assembly parts  |
| Distance between fixing points          | 475 mm  |
| To fit door width                       | 600 mm  |
| VX installation options                 | In door width 600 mm  |
| VX SE installation options              | In door width 600 mm  |
| AX installation options                 | In enclosure width 500 mm and in enclosure height 600 mm, in conjunction with rail for interior installation AX<br>In enclosure width 1200 mm, in lockable door |
| AX stainless steel installation options | In enclosure height 600 mm  |
| Installation options, AX plastic        | In door width 600 mm  |

# Features

|                                    |  |
|------------------------------------|--|
| Installation options for 3-part AX | In the enclosure depth 673 mm or in the width of the wall section  |
| PC installation options            | In door width 600 mm   |
| CX installation options            | In door width 600 mm   |
| Assembly instruction               | For installation in AX sheet steel, only in conjunction with rail for interior installation AX   |
| Note                               | For installing your own components on the punched section with mounting flange, metal screws or self-tapping M5 screws are required                                  |
| To fit                             | Enclosure type: VX<br>VX SE<br>PC<br>AX<br>AX wall-mounted enclosure, 3-part<br>CX one-piece console<br>CX pedestal<br>Suitable for width or height or depth: 600 mm |
| Packs of                           | 4 pc(s).   |
| Net weight                         | 0.956 kg   |
| Gross weight                       | 1.14 kg  |
| Customs tariff number              | 73269098   |
| ETIM 9                             | EC002620   |
| ECLASS 8.0                         | 27189234   |
| Product description                | VX Punched section, with mounting flange 14 x 39 mm, for door width: 600 mm  |

# Approvals

|              |                 |
|--------------|-----------------|
| Explanations | PCF-declaration |
|--------------|-----------------|