

# Rittal – The System.

Faster – better – everywhere.



## DK 5302.016 Air baffle plate

State: 2/06/2026 (Source: [rittal.com/uk-en](http://rittal.com/uk-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 5302.016 - Air baffle plate for VX IT 482.6 mm (19") mounting angles, standard

To separate the hot/cold zones within an enclosure with aisle containment or when using an LCP system.



## Features

|                 |                                                                                                                                                                                         |
|-----------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Model No.       | DK 5302.016                                                                                                                                                                             |
| Benefits        | To selectively boost the energy efficiency of your climate control system<br>Vertical brush strip for collision-free shielding with installed rail systems on the outer mounting level. |
| Applications    | To separate the hot/cold zones within an enclosure with aisle containment or when using an LCP system.                                                                                  |
| Material        | Sheet steel<br>Blanking panel: Plastic, UL 94-HB, halogen-free<br>Brush strip: Plastic, UL 94-HB                                                                                        |
| Surface finish  | Spray-finished                                                                                                                                                                          |
| Colour          | RAL 9005                                                                                                                                                                                |
| Supply includes | 2 vertical trim panels<br>2 horizontal trim panels<br>4 brush strips<br>4 cellular PU foam pieces<br>Assembly parts                                                                     |

# Features

|                               |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |
|-------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Assembly instruction          | <p>The vertical trim panels with brush strip may be fitted on both the front and rear 482.6 mm (19") mounting angles for partitioning. The horizontal trim panels with brush strips can only be mounted on the front 482.6 mm (19") mounting angles.</p> <p>482.6 mm (19") mounting cut-outs integrated within the partitioning areas may optionally be sealed with the supplied blanking panels, or used to install additional components or for cable routing. Please see the product-specific scope of supply.</p> |
| To fit                        | <p>Width: = 600 mm<br/>Height: = 2,000 mm</p>                                                                                                                                                                                                                                                                                                                                                                                                                                                                         |
| Packs of                      | 1 pc(s).                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              |
| Net weight                    | 2.06 kg                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                               |
| Gross weight                  | 2.66 kg                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                               |
| PCF per pack (cradle-to-gate) | 10.1 kg CO2 eq (Cat B)                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                |
| Note on PCF category          | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared                                                                                                                                                                                                                                                                                                                                                                                                        |
| Customs tariff number         | 56090000                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              |
| ETIM 9                        | EC000331                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              |
| ECLASS 8.0                    | 27189272                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              |
| Product description           | Air baffle plate, for VX IT 19" mounting angles, standard, to separate the hot/cold zones within an enclosure with aisle containment or when using an LCP system. WxH: 600x2000 mm, RAL 9005                                                                                                                                                                                                                                                                                                                          |