


Rittal – The System.

Faster – better – everywhere.



CP 6510.330

Support arm, height-adjustable

State: 26/07/2025 (Source: rittal.com/uk-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



CP 6510.330 - Support arm, height-adjustable for support arm systems CP 120

Offers enhanced ergonomics

Features

Model No.	CP 6510.330
Product description	Offers enhanced ergonomics thanks to adjustment range for tall and short operators, for seated and standing work adjustable to up to 800 mm as required via an adjustment screw at the front of the support arm. Clip-off plastic panels for access to integral cable routing.
Benefits	<p>Precise coordination of the compression spring to the enclosure weight via an adjusting screw at the rear of the support arm</p> <p>Complete functional reliability – if the compression spring breaks, the arm will remain in position</p> <p>Tilting angle of the mounted enclosure is identical in every height position</p> <p>Cables with connectors such as DVI, VGA are easily inserted</p> <p>Integral locking in three stages</p>
Colour	RAL 9006
Supply includes	Assembly parts
Length	1,090 mm
Installation options	<p>Maximum cross-section for cable entry 18 x 39 mm</p> <p>Maximum number of cables that may be inserted: 3x Ø 7 mm and 2x Ø 8.5 mm</p>
Note on Model No.	Weight range applies to configured enclosure and vertical support section.
Dimensions	Length: 1,090 mm
Load capacity	15 kg...32 kg
Packs of	1 pc(s).
Net weight	18

Features

Gross weight	19
Customs tariff number	73269098
EAN	4028177598140
ECLASS 8.0	27189263

Approvals

Explanations	Manufacturer's declaration
--------------	----------------------------

Tender text

Support arm, height adjustable for support arm systems CP 120
Support arm, height adjustable offers enhanced ergonomics thanks to Adjustment range, for tall and short operators, for seated and standing work. Adjustable to a maximum of 800 mm as required via an adjusting screw at the front of the support arm. Complete functional reliability - if the compression spring breaks, the arm will remain in position. Clip-off plastic panels for access to integral cable routing. Tilting angle of the mounted enclosure is identical in every height position.

Weight/pack: 19 kg

Weight range: 15 - 32 kg

Weight range applies to configured enclosure and vertical support section.

Colour: RAL 9006

Length: 1090 mm

Model No: 6510330

producer: Rittal GmbH & Co. KG