


Rittal – The System.

Faster – better – everywhere.



DK 5501.665

Component shelf, static installation

State: 11/05/2026 (Source: rittal.com/uk-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 5501.665 - Component shelf, static installation for VX IT, TS IT, TE, TX CableNet

For static installation between two 482.6 mm (19") mounting levels.

Features

| | |
|-------------------------------|--|
| Model No. | DK 5501.665 |
| Benefits | Tool-free, time-saving one-man assembly |
| Applications | Depth-variable to adapt to individual distances between levels |
| Material | Sheet steel |
| Surface finish | Spray-finished |
| Colour | RAL 9005 |
| Supply includes | Assembly parts |
| Installation options | 482.6 mm (19") L mounting angles, front and rear 482.6 mm (19") mounting frames front and rear |
| Load capacity | 50 kg |
| Dimensions | Width: 484 mm |
| To fit | Enclosure type: VX IT TS IT TE TX CableNet |
| Distance between levels | 600 - 900 mm |
| Packs of | 1 pc(s). |
| Net weight | 6.47 kg |
| Gross weight | 6.62 kg |
| PCF per pack (cradle-to-gate) | 17.7 kg CO2 eq (Cat B) |
| Note on PCF category | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number | 73269098 |

Features

| | |
|---------------------|---|
| ETIM 9 | EC002620 |
| ECLASS 8.0 | 27189261 |
| Product description | DK Component shelf, WxH: 484 mm x 0,5 U, 50 kg, distance between levels: 600-900 mm, depth-variable, RAL 9005 |

Tender text

482.6 mm (19") - component shelf, static installation
Depth-variable perforated component shelf, pull-out, for L-shaped mounting angles and similar mounting angle shapes. For static installation between two 482.6 mm (19") mounting levels.

Depth-variable to adapt to individual distances between levels from 600 to 900 mm.

Tool-free, time-saving one-man assembly from the enclosure front.

Locate, pull-out, snap into position.

Perforated component shelf surface to support climate control inside the enclosure.

Load capacity 50 kg. Component shelf height 1/2 U.

Material: Sheet steel

Surface finish: Spray-finished

Colour: RAL 9005

Model No DK: 5501.665

Manufacturer: Rittal