

Rittal – The System.

Faster – better – everywhere.



CP 6315.100

Operating housing with handle strips

State: 2/24/2026 (Source: [rittal.com/us-en](https://www.rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



CP 6315.100 - Operating housing with handle strips

Command panel with handle strips in contemporary design of sheet steel, with Ø 130 mm support arm cut-out to fit CP 60/120/180 support arm system, service access optionally from the front or rear, aluminum front panel easily removable for machining, protection category IP 55



Features

Model No.	CP 6315.100
Material	Housing and door: Carbon steel Handle strips: Aluminum Front panel: Aluminum Cover caps: Plastic
Surface finish	Housing and door: Dipcoat primed, powder-coated on the outside, textured paint Handle strip: Natural anodized Front panel: Natural anodized.
Color	Housing and door: RAL 7035 Handle strip: Natural anodized Front panel: Natural anodized. Cover caps: Similar to RAL 7024
Supply includes	Housing with cut-out and reinforcement for support arm connection Ø 130 mm Front with maximum cut-out, covered with easily machinable 3 mm aluminum front panel Side handle strips and cover caps Cam lock with 3 mm double-bit insert Integral interior mounting bracket with TS system punchings

Features

Dimensions	Width: 300 mm Height: 300 mm Depth: 210 mm Width: 11.8 " Height: 11.8 " Depth: 8.27 "
Protection category IP to IEC 60529	IP 55
Version	Service access from front
Note	The support arm connection and door catch may be swapped over by rotating the enclosure Optional: Support arm connection Ø 130 mm, preformed off-center in the reinforcement plate, easily drilled out Lock systems for servicing access from the front: 41 mm lock inserts, type C, lock cylinder, plastic handles and T-handles, type C
Base material	Aluminum
Note on Model No.:	Compatible mounting plate 5050.432 with shipping bag 5050.507
Lock	Lock version: Sickle-shaped locking nose No. of locks: 1 Lock Insert: 3 mm double-bit
Packaging unit	1 pc(s).
Net weight	6.958 kg
Gross weight	7.324 kg
Customs tariff number	94032080
ECLASS 8.0	27180505
Product description	CP Operating housing with handle strips, WHD: 300x300x210 mm, Sheet steel, handle strips made of aluminum, Servicing access from the front

Approvals

Approvals

Explanations

Declaration of conformity

Declaration of conformity UK