

# Rittal – The System.

Faster – better – everywhere.



## CS 9783.530

## Outdoor Basic enclosure

State: 5/31/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# CS 9783.530 - Outdoor Basic enclosure

Single-walled housing systems, one-door and two-door. Ready for use for all applications with passive interior equipment or low power dissipation in outdoor areas. Roof concept with all-round louvred grilles



## Features

Model No.	CS 9783.530
Product description	Outdoor housing with 100 mm transport base/plinth and rain canopy projecting on all sides.
Material	Aluminum AlMg3
Surface finish	Powder-coated UV-resistant pure polyester
Color	RAL 7035
Supply includes	Single-walled outdoor enclosure, fully preconfigured Basic enclosure with gland plate, three-part 25 mm system punchings in the roof, base, front and in the enclosure depth Front door(s) with door stay, swing lever handle and semi-cylinder, lock BJ20027 Transport plinth with screw-fastened trim panels front and rear Rain canopy

# Features

---

Dimensions	Width: 600 mm Height: 1,200 mm Depth: 500 mm Width: 23.6 " Height: 47.2 " Depth: 19.7 "
------------	--

---

Dimensions	Overall height: 1,355 mm Rain canopy width: 650 mm Rain canopy height: 55 mm Rain canopy depth: 550 mm Clearance width: 512 mm Clearance height: 1,112 mm Clearance depth: 449 mm Height of base/plinth: 100 mm Rain canopy width: 25.6 " Rain canopy height: 2.17 " Rain canopy depth: 21.7 " Clearance width: 20.2 " Clearance height: 43.8 " Clearance depth: 17.7 " Height of base/plinth: 3.94 "
------------	---

---

Number of doors	1
-----------------	---

---

Type rating according to UL 50E	Type 3R
---------------------------------	---------

---

Protection category IP to IEC 60 529	IP 55
--------------------------------------	-------

---

IK code	IK10
---------	------

---

Base material	Aluminum
---------------	----------

---

Packaging unit	1 pc(s).
----------------	----------

---

Net weight	30 kg
------------	-------

---

Gross weight	35 kg
--------------	-------

---

Customs tariff number	94032080
-----------------------	----------

---

ETIM 9	EC000261
--------	----------

---

ECLASS 8.0	27180101
------------	----------

---

# Features

---

Product description

Outdoor basic enclosure, WHD: 600x1,200x500 mm, aluminum, with 100 mm transport base/plinth and rain canopy, single door on front

# Approvals

---

Explanations

Declaration of conformity