

# Rittal – The System.

Faster – better – everywhere.

## ► Skriňa na stenu AE s 19" profilovými lišťami, hĺbková variabilita – DK 7645.000

Date : 28.9.2020

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# Skriňa na stenu AE s 19" profilovými lištami, hĺbková variabilita – DK 7645.000

created: 28.09.2020 build on [www.rittal.com/sk-sk](http://www.rittal.com/sk-sk)



Discontinued article.

## Product description

<b>Description:</b>	Wall-mounted enclosure for small networks with a high protection category.
<b>Material:</b>	Enclosure: Sheet steel
<b>Surface finish:</b>	Enclosure: Powder-coated Mounting angles: Zinc-plated
<b>Colour:</b>	RAL 7035
<b>Protection category IP to IEC 60 529:</b>	Up to IP 66 (depending on the selected gland pate)
<b>Supply includes:</b>	Enclosure with hinged door Door hinged on the right, may be swapped to the left Cam lock with 3 mm double-bit insert Gland plate with brush strip for cable entry in the enclosure base Mounting angles, 482.6 mm (19"), fully depth adjustable C rail, for cable clamping on the rear panel Metal bracket for optional accommodation of an earth rail or 482.6 mm (19") socket strip
<b>Basic material:</b>	oceľový plech

## Product features

<b>Dimensions:</b>	Width: 600 mm Height: 760 mm Depth: 350 mm
--------------------	--

<b>Installation height for components:</b>	16 U
<b>Installation depth:</b>	310 mm
<b>Door hinge:</b>	right, may be swapped to the left
<b>Number of cam locks:</b>	2
<b>Gland plate, size:</b>	5
<b>Gland plate, qty.:</b>	1
<b>Packs of:</b>	1 pc(s).
<b>Weight/pack:</b>	32,2 kg
<b>EAN:</b>	4028177147041
<b>Customs tariff number:</b>	94032080
<b>ETIM 7.0:</b>	EC002500
<b>ETIM 6.0:</b>	EC002500
<b>eCl@ss 8.0/8.1:</b>	27180208
<b>eCl@ss 6.0/6.1:</b>	27180208
<b>Product description:</b>	DK Wall-mounted enclosures AE, WHD:600x760x350 mm, 16 U, AE 1376

## Approvals

<b>Approvals:</b>	Lloyds Register of Shipping NA VDE
-------------------	--