



Certificate of Compliance

Certificate: 2155017

Master Contract: 153184 (059132_0_000)

Project: 70124264

Date Issued: July 05, 2017

Issued to: Rittal GmbH & Co. KG
Auf dem Stuetzelberg
Herborn, 35745
GERMANY
Attention: Thorsten Heimberg

The products listed below are eligible to bear the CSA Mark shown



Issued by: Nico Bos
Nico Bos

PRODUCTS

CLASS 1211 03 - COMFORT CONDITIONING EQUIPMENT – Central Type, Air Handling Equipment

Air Water Heat Exchangers described below are components units, where the acceptability of the combination is determined by CSA International; intended for indoor use, to be mounted inside or outside the electronic equipment enclosure as per the installation instructions provided with the units.

Part A – Permanently connected, Air to water heat exchangers Wall mounted Models

Temperature rating: Ambient: 70°C

SK 3214100 230 V, 50/60 Hz, 36/37 W

SK 3214115 115 V, 50/60 Hz,

SK 3215100 230 V, 50/60 Hz, 83/85 W

SK 3215115 115 V, 50/60 Hz,

SK 3216100 230 V, 50/60 Hz, 222/248 W

SK 3216115 115 V, 50/60 Hz,

SK 3216480 480 V, 50/60 Hz,

SK 3217100 230 V, 50/60 Hz, 86/81 W

SK 3217115 115 V, 50/60 Hz,

SK 3218100 230 V, 50/60 Hz, 91/109 W

SK 3218104 230 V, 50/60 Hz, 91/109 W : Stainless steel 304 core structure of heat exchanger

SK 3218115 115 V, 50/60 Hz,



Certificate: 2155017
Project: 70124264

Master Contract: 153184
Date Issued: July 05, 2017

Part B – Permanently connected, Air to water heat exchangers, Roof mounted models SK3209.100, SK3209.110, SK3209.140, SK3209.500, SK3209.510, SK3209.540, SK3210.100, SK3210.110, SK3210.140, SK3210.500, SK3210.510 and SK3210.540.

Part C – Permanently connected, Air to water heat exchanger, wall mounted models SK3363.100, SK3363.104, SK3363.110, SK3363.114, SK3363.140, SK3363.144, SK3363.500, SK3363.504, SK3363.510, SK3363.514, SK3363.540, SK3363.544, SK3364.100, SK3364.104, SK3364.110, SK3364.114, SK3364.140, SK3364.144, SK3364.500, SK3364.504, SK3364.510, SK3364.514, SK3364.540, SK3364.544, SK3373.100, SK3373.104, SK3373.110, SK3373.114, SK3373.140, SK3373.144, SK3373.500, SK3373.504, SK3373.510, SK3373.514, SK3373.540, SK3373.544, SK3374.100, SK3374.104, SK3374.110, SK3374.114, SK3374.140, SK3374.144, SK3374.500, SK3374.504, SK3374.510, SK3374.514, SK3374.540, SK3374.544, SK3375.100, SK3375.104, SK3375.110, SK3375.114, SK3375.140, SK3375.144, SK3375.500, SK3375.504, SK3375.510, SK3375.514, SK3375.540 and SK3375.544.

Part D – Permanently connected, miscellaneous heating and cooling equipment, air to water heat exchanger.
Temperature rating: Ambient: 70°C
SK 3214.700 230 V, 50/60 Hz, 36/37 W
SK 3215.700 230 V 50/60 Hz, 83/85 W

APPLICABLE REQUIREMENTS

CSA C22.2 No. 236-15 – Heating and cooling equipment



Supplement to Certificate of Compliance

Certificate: 2155017

Master Contract: 153184 (059132_0_000)

*The products listed, including the latest revision described below,
are eligible to be marked in accordance with the referenced Certificate.*

Product Certification History

Project	Date	Description
70124264	2017-07-05	Update to report 2155017 to add new model numbers: SK 3214.700, SK 3215.700.
70014248	2014-12-19	Update to report 2155017 for filter revision.
70002048	2013-09-24	Update to report 2155017 to add components based on UL report.
2155017	2009-04-23	Review and accept UL Test Data for Canadian Certification.