

CERTIFICATE OF COMPLIANCE

Certificate Number 20150306 – E170282
Report Reference E170282 - 20000911
Issue Date 2015-MARCH-06

Issued to: RITTAL CORP
1 Rittal PI
Urbana, OH 43078-5003 USA

This is to certify that representative samples of Industrial Control Panels
USL, CNL - Industrial control panel enclosures, TS8 Series,
DK-TS, TS8 3- Door FMDC and SV-TS8.

USL, CNL - Type 12 Sealing Frame Field Installation
Accessory Kit
(See following pages for additional information.)

Have been investigated by UL in accordance with the
Standard(s) indicated on this Certificate.

Standard(s) for Safety: UL 508A, "Industrial Control Panels."
CSA-C22.2 No. 14, "Industrial Control Equipment."

Additional Information: See the UL Online Certifications Directory at
www.ul.com/database for additional information

Only those products bearing the UL Certification Mark should be considered as being covered by UL's
Certification and Follow-Up Service.

Look for the UL Certification Mark on the product.



Bruce Mahrenholz, Assistant Chief Engineer, Global Inspection and Field Services

UL LLC

Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL. For questions, please
contact a local UL Customer Service Representative at www.ul.com/contactus



CERTIFICATE OF COMPLIANCE

Certificate Number 20150306 – E170282
Report Reference E170282 - 20000911
Issue Date 2015-MARCH-06

This is to certify that representative samples of the product as specified on this certificate were tested according to the current UL requirements.

Additional Information


Ratings:

Type 1	TS8 (including stainless steel)	DK-TS	SV-TS8
Maximum Height	2400 mm	2400 mm	2200 mm
Maximum Width	1800 mm	1800 mm	800 mm
Maximum Depth	1000 mm	1000 mm	800 mm
Maximum Width with glass viewing door	600 mm	600 mm	600 mm

Type 3R	TS8 (including stainless steel)
Maximum Height	2200 mm
Maximum Width (Single door)	1000 mm
Maximum Depth	800 mm
Maximum Height (Double door)	2000 mm
Maximum Width (Double door)	1800 mm

Type 4	TS8
Maximum Height	2000 mm
Maximum Width (Single door)	900 mm
Maximum Depth	800 mm

Type 4X	TS8 (only stainless steel)
Maximum Width	2000 mm
Maximum Width (Single door)	900 mm
Maximum Depth	800 mm



Bruce Mahrenholz, Assistant Chief Engineer, Global Inspection and Field Services

UL LLC

Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL. For questions, please contact a local UL Customer Service Representative at www.ul.com/contactus



CERTIFICATE OF COMPLIANCE

Certificate Number 20150306 – E170282
Report Reference E170282 - 20000911
Issue Date 2015-MARCH-06

Type 12	TS8 (including stainless steel)	DK-TS	FMDC 3-DOOR
Maximum Height	2400 mm	2400 mm	2400 mm
Maximum Width (double door)	1800 mm	1800 mm	2100 mm
Depth	1200 mm	1200 mm	1000 mm
Maximum Width (single door)	1000 mm	1000 mm	
Maximum Depth	1200 mm	1200 mm	
Type 3R/4X/12 (Ref ILL 27)	TS8 (only stainless steel)		
Maximum Height	2200 mm		
Maximum Width	800 mm		
Maximum Depth	800 mm		



Bruce Mahrenholz, Assistant Chief Engineer, Global Inspection and Field Services

UL LLC

Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL. For questions, please contact a local UL Customer Service Representative at www.ul.com/contactus

