

# Rittal – The System.

Faster – better – everywhere.

## ► Blue e Top Therm air conditioners



Ready for quick delivery and installation, these energy-saving air conditioning units from 1,700 BTU to 16,800 BTU (500 to 4000 W) target energy savings of 45 percent or more. Our industry-leading intelligent Eco-mode control keeps these high-efficiency units performing well above expectations, while nanotechnology repels dirt, oil and other contaminants from the condenser coils.

On the reverse side are a series of the most popular sizes and configurations.

For complete details on the entire line, go to [www.rittal.us](http://www.rittal.us).

### Rittal TopTherm cooling units – Guaranteed output

TÜV-tested output to DIN EN 14511

Rittal is the only supplier in the world to deliver its entire range of enclosure cooling units tested to the latest DIN EN standard.

All TopTherm cooling units in the output range from 500 to 4,000 W are tested to DIN EN 14511:2012-01 standard by the independent test institute TÜV NORD, and are authorized to carry the relevant test mark for the entire series.

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

[www.rittal.us](http://www.rittal.us)



## Roof-mounted air conditioner

RAL 7035 Part No.	Total Cooling Output BTU (WATTS)	Dimensions H x W x D inches (mm)	Voltage V, Hz	
3382.500	2116 (620)	16 x 24 x 15 (417 x 597 x 380)	230, 50/60	
3382.510			115, 50/60	
3359.500	2696 (790)		230, 50/60	
3359.510			115, 50/60	
3359.540			400, 2~, 50/60	
3383.500	3715 (1090)		230, 50/60	
3383.510			115, 50/60	
3383.540			400, 2~, 50/60	
3384.500	5630 (1650)		16 x 24 x 19 (417 x 597 x 475)	230, 50/60
3384.510				115, 50/60
3384.540		400, 2~, 50/60		
3385.500	7302 (2140)	230, 50/60		
3385.510		115, 50/60		
3385.540		400, 2~, 50/60		
3386.540	11,260 (3300)	19 x 31 x 23 (470 x 796 x 580)		400, 3~, 50 460, 3~, 60
3387.540	13,649 (4000)			400, 3~, 50 460, 3~, 60

## Wall-mounted air conditioner

RAL 7035 Part No.	Total Cooling Output BTU (WATTS)	Dimensions H x W x D inches (mm)	Voltage V, Hz	
3302.100	1296 (300)	22 x 11 x 6 (550 x 280 x 140)	230, 50/60	
3302.110			115, 60	
3303.500	2252 (660)	22 x 11 x 8 (550 x 280 x 210)	230, 50/60	
3303.510			115, 50/60	
3361.500	3036 (890)	22 x 11 x 11 (550 x 280 x 280)	230, 50/60	
3361.510			115, 50/60	
3361.540			400, 2~, 50/60	
3304.500	4265 (1250)	37 x 16 x 10 (950 x 400 x 260)	230, 50/60	
3304.510			115, 50/60	
3304.540			400, 3~, 50 460, 3~, 60	
3305.500	6005 (1760)		230, 50/60	
3305.510			115, 50/60	
3305.540			400, 3~, 50 460, 3~, 60	
3328.500	8735 (2560)		62 x 16 x 12 (1580 x 400 x 295)	230, 50/60
3328.510				115, 50/60
3328.540				400, 3~, 50 460, 3~, 60
3329.500	9247 (2710)			230, 50/60
3329.510		115, 50/60		
3329.540		400, 3~, 50 460, 3~, 60		
3332.540	14,843 (4350)	62 x 20 x 13 (1580 x 500 x 340)		400, 3~, 50 460, 3~, 60

### Rittal Corporation

Woodfield Corporate Center  
 425 North Martingale Road, Suite 400 • Schaumburg, Illinois 60173  
 Phone: 937-399-0500 • Toll-free: 800-477-4000  
 Email: rittal@rittal.us • Website: www.rittal.us

**Note:** Imperial measurements are approximate, metric measurements are exact.