


Enclosures

IT enclosure systems

Network/server enclosures TS IT

with glazed door, with 482.6 mm (19") mounting frame, width 600 mm




Model No. DK	U	Width dimensions mm			Height dimensions mm		Depth dimensions mm						
		B1	B2	B3	H1	H2	T1	T2	T3	T4	T5	T6	T7
5508.141	42	597	535	512	1998.5	1912	1024	912	935	745	84	1111	850
5510.141	42	597	535	512	1998.5	1912	1224	912	935	745	144	1311	1050
5513.141	47	597	535	512	2198.5	2112	1024	912	935	745	84	1111	850
5515.141	47	597	535	512	2198.5	2112	1224	1112	1135	745	144	1311	1050
5526.141	24	597	535	512	1198.5	1112	624	512	535	345	84	711	–
5527.141	38	597	535	512	1798.5	1712	624	512	535	345	84	711	–
5528.141	38	597	535	512	1798.5	1712	824	712	735	545	84	911	650
5529.141	42	597	535	512	1998.5	1912	624	512	535	345	84	711	–
5530.141	42	597	535	512	1998.5	1912	824	712	735	545	84	911	650
5531.141	47	597	535	512	2198.5	2112	824	712	735	545	84	911	650


Network/server enclosures TS IT

with glazed door, with 482.6 mm (19") mounting frame, width 800 mm


Front view




Front view without door




Side view




Rear view




Top view



Section A – A



Top view, depth 600 mm



Enclosure

- B1 = Overall width
- B2 = Roof attachment spacing
- B3 = Clearance of enclosure frame
- H1 = Overall height
- H2 = Clearance of enclosure frame
- T1 = Overall depth
- T2 = Clearance of enclosure frame
- T3 = Roof attachment spacing
- T4 = Distance between 482.6 mm (19") levels
- T5 = Distance between frame and 482.6 mm (19") level
- T6 = Overall depth with handles
- T7 = Length of brush strips

1 For height 1200 mm one-piece door

Note:

- With fitted side panels, the overall width (B1) is increased by 9 mm.
- Between bayed enclosures, allow 3 mm for the seal.

Model No. DK	U	Width dimensions mm			Height dimensions mm		Depth dimensions mm						
		B1	B2	B3	H1	H2	T1	T2	T3	T4	T5	T6	T7
5503.141	24	797	735	712	1198.5	1112	824	712	735	545	147	911	650
5504.141	24	797	735	712	1198.5	1112	1024	912	935	745	87	1111	850
5505.141	38	797	735	712	1798.5	1712	824	712	735	545	147	911	650
5506.141	42	797	735	712	1998.5	1912	624	512	535	445	87	711	-
5507.141	42	797	735	712	1998.5	1912	824	712	735	545	147	911	650
5509.141	42	797	735	712	1998.5	1912	1024	912	935	745	87	1111	850
5511.141	42	797	735	712	1998.5	1912	1224	1112	1135	745	147	1311	1050
5512.141	47	797	735	712	2198.5	2112	824	712	735	545	147	911	650
5514.141	47	797	735	712	2198.5	2112	1024	912	935	745	87	1111	850
5516.141	47	797	735	712	2198.5	2112	1224	1112	1135	745	147	1311	1050