

Rittal – The System.

Faster – better – everywhere.

► Compact enclosures AE Stainless steel – AE 1017.600

Date : Jun 6, 2023

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Compact enclosures AE Stainless steel – AE 1017.600

created: 06.06.2023 on www.rittal.com/com-en



Product description

Material:	Enclosure: Stainless steel Door: Stainless steel, all-round foamed-in PU seal Mounting plate: Sheet steel Stainless steel 1.4301 (AISI 304) Lock insert: Stainless steel 1.4301 (AISI 304)
Surface finish:	Enclosure and door: Brushed, grain 400, peak-to-valley height < 0.8 µm Mounting plate: Zinc-plated
Protection category IP to IEC 60 529:	IP 66
Protection category NEMA:	NEMA 4X
IK Code:	IK08
Supply includes:	Enclosure with door(s) Mounting plate Lock: 3 mm double-bit 3-point lock system
Basic material:	Stainless steel

Product description

Dimensions:	Width: 800 mm Height: 1200 mm Depth: 300 mm
Mounting plate:	Width: 740 mm Height: 1155 mm

Number of doors:	1
Lock version:	3-point lock system
Number of locks:	1
Lock insert:	3 mm double-bit
Packs of:	1 pc(s).
Weight/pack:	61.5 kg
EAN:	4028177000612
Customs tariff number:	94032080
ETIM 7.0:	EC000261
ETIM 6.0:	EC000261
eCl@ss 8.0/8.1:	27180101
eCl@ss 6.0/6.1:	27180101
Product description:	AE Compact enclosure, WHD: 800x1200x300 mm, Stainless steel 1.4301, with mounting plate, single-door, 3-point lock system

Approvals

Approvals:	DNV-GL Lloyds Register of Shipping RRR UL + C-UL
Certificates:	IK-Code NA Protection category
Declarations:	Declaration of conformity