

RITTAL THERM QUESTIONNAIRE



Company name

Contact

Telephone no.

Email

[Click here for THERM ONLINE](#)

Enclosure Details

Rittal Part No. (if available) Dimensions W (mm) H (mm) D (mm)

Enclosure IP Rating (if known) Enclosure Type Location

Position:



1. Single enclosure, free-standing on all sides



2. Single enclosure for wall mounting



3. First or last enclosure in a suite, free-standing



4. First or last enclosure in a suite, for wall mounting



5. Enclosure within a suite, free-standing



6. Enclosure within a suite, for wall mounting



7. Enclosure within a suite, for wall mounting with covered roof area

Temperature Info

Required Enclosure internal temperature:

Minimum, °C

Maximum, °C

Ambient Temperature:

Minimum, °C

Maximum, °C

If the heat loss of the electrical equipment is not known, please provide the actual temperatures of the installation.

Heat loss of equipment, W

(If known)

OR

Actual installation temperatures:

Inside Enclosure, °C

Ambient, °C

Equipment details

Desired Supply Voltage:

115V

230V

400V

460V

Other

If other, please specify

Ambient Environment:

Humid

Dusty

Salty

Wet

Oily

Preferred Equipment:

Fans & Filters

Air/Air Heat Exchange

Air/Water Heat Exchanger

Cooling Unit

Preferred positions of Cooling:

Roof

Door

Side Wall

No preference

Other Project Details:

Would you like to discuss service options

Email form to: COOLING@RITTAL.CO.UK