

Rittal – The System.

Faster – better – everywhere.

Enclosure heater without fan – SK 3105.370

Date : Sep 29, 2020

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Enclosure heater without fan – SK 3105.370

created: 29.09.2020 on www.rittal.com/com-en



Product description

Description: Enclosure heaters to regulate relative humidity, prevent temperatures from dropping below the dew point and stop condensation forming inside the enclosure. This prevents consequential damage associated with corrosion or electrical short circuits.

Material: Aluminium, anodised

**Protection category
IP to IEC 60 529:** IP 20

Supply includes: PTC heater
Quick-connection terminal
Assembly parts

Note: A thermostat is recommended for precise temperature control inside the enclosure. In order to prevent condensation on assemblies, a hygostat is recommended to regulate heating
In larger enclosures, even heat distribution is best achieved by installing several low-output heaters.

Note on Model No.: Special voltages available on request. We reserve the right to make technical modifications.

Product features

**Continuous thermal
output at 10 °C:** 130 W - 150 W

**Rated operating
voltage:** 110 V - 240 V, 1~, 50 Hz/60 Hz

Dimensions: Width: 90 mm
Height: 180 mm
Depth: 75 mm

Miniature circuit-breaker/fuse:	4 A
eCl@ss 8.0/8.1:	27180710
Packs of:	1 pc(s).
Weight/pack:	0.9 kg
EAN:	4028177638679
Customs tariff number:	85162999
ETIM 7.0:	EC000737
ETIM 6.0:	EC000737
eCl@ss 8.0/8.1:	27180710
eCl@ss 6.0/6.1:	27180710
Product description:	SK enclosure heater, without fan, 130-150 W, 110-240 V, 1~, 50/60 Hz, WHD: 90 x 180 x 75 mm

Approvals

Approvals:	Approval overview VDE	CSA UR + C-UR
Certificates:	EAC	
Declarations:	Declaration of conformity	