CERTIFICATE

Issued to: Applicant: Rittal GmbH & Co. KG Auf dem Stützelberg 18 35745 Herborn, Germany

Product	:	Fixed general purpose luminaire with LEDs
Trade name	:	RITTAL
Туре	:	SZ 2500220

The product and any acceptable variation thereto is specified in the Annex to this certificate and the documents therein referred to.

DEKRA hereby declares that the above-mentioned product has been certified on the basis of:

- a type test according to the standard EN 60598-1:2015; EN 60598-2-1:1989; EN 62031:2008;
- an inspection of the production location according to CENELEC Operational Document CIG 021
- a certification agreement with the number 2133829

DEKRA hereby grants the right to use the ENEC KEMA-KEUR certification mark.

The ENEC KEMA-KEUR certification mark may be applied to the product as specified in this certificate for the duration of the ENEC KEMA-KEUR certification agreement and under the conditions of the ENEC KEMA-KEUR certification agreement.

This certificate is issued on: 14 September 2016 and expires upon withdrawal of one of the above mentioned standards.

Certificate number: 3406238.02

DEKRA Certification B.V.

drs. G.J. Zoetbrood Managing Director

J. Marggraf Certification Manager

© Integral publication of this certificate is allowed

ACCREDITED BY THE DUTCH ACCREDITATION COUNCIL







DEKRA Certification B.V. Meander 1051, 6825 MJ Arnhem P.O. Box 5185, 6802 ED Arnhem The Netherlands T +31 88 96 83000 F +31 88 96 83100 www.dekra-certification.com Registered Arnhem 09085396



ANNEX TO ENEC KEMA-KEUR CERTIFICATE 3406238.02

page 1 of 1

SPECIFICATION OF THE CERTIFIED PRODUCT

Product data

product Fixed general purpose luminaire with LEDs 2 trade name RITTAL type SZ 2500220 • rated voltage 24 V 2 nature of supply dc 11 W rated input : ambient temperature range : -20 °C...+55 °C class : Ш degree of protection IP20 5

Additional information

- luminaire for LED control cabinet lighting with built-in LED module and switch

- the light source is non-user replaceable

- to be connected to supply via appliance inlet

TESTS

Test requirements

EN 60598-1:2015 EN 60598-2-1:1989

Additional test requirements:

EN 62031:2008 + A1:2013 + A2:2015

Test result

The test results are laid down in DEKRA test file 3406238.00.

Remarks

The component list is laid down in test report 3406237.51. This certificate is derived from ENEC/KEMA-KEUR certificate no. 3406237.02.

Conclusion

The examination proved that all test requirements were met.

Tested by : R. Schomacker

Checked by : M. Müller