

Rittal – The System.

Faster – better – everywhere.

Baying systems TS 8 – TS 8206.500

Date : Oct 15, 2019

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Baying systems TS 8 – TS 8206.500

created: 15.10.2019 on www.rittal.com/com-en



Discontinued article.

This item will be discontinued on: 15.02.2019 |||This item is being replaced by: 8206000

Product description

Material:	Enclosure frame: Sheet steel, 1.5 mm Roof: Sheet steel, 1.5 mm Door: Sheet steel, 2.0 mm Rear panel: Sheet steel, 1.5 mm Gland plates: Sheet steel, 1.5 mm Mounting plate: Sheet steel, 3.0 mm
Surface finish:	Enclosure frame: Dipcoat-primed Door, roof and rear panel: Dipcoat-primed, powder-coated on the outside, textured paint Mounting plate and gland plates: Zinc-plated
Colour:	RAL 7035
Protection category IP to IEC 60 529:	IP 55
Protection category NEMA:	NEMA 12
IK Code:	IK09
Supply includes:	Enclosure frame Door(s) R/h door hinge with single-door enclosures, may be swapped to opposite side Roof plate Rear panel 4 eyebolts Lock: 3 mm double-bit Gland plates Mounting plate 2 TS punched rails 18 x 38 mm 2 support strips fitted in the enclosure depth

Product modification:	TS 8 and the SE 8 both come with the new mounting plate of the baying enclosure system VX25.
Basic material:	Sheet steel
Product features	
Dimensions:	Width: 1200 mm Height: 2000 mm Depth: 600 mm
Mounting plate:	Width: 1099 mm Height: 1896 mm
Number of doors:	2
2 support strips fitted in the enclosure depth:	yes
Packs of:	1 pc(s).
Weight/pack:	194.6 kg
EAN:	4028177250888
Customs tariff number:	94032080
ETIM 6.0:	EC000261
ETIM 5.0:	EC000261
eCl@ss 8.0/8.1:	27180101
eCl@ss 7.0/7.1:	27180101
eCl@ss 6.0/6.1:	27180101
eCl@ss 5.1/5.1.4:	27180101
Product description:	TS Bayed enclosure system, WHD: 1200x2000x600 mm, Sheet steel, with mounting plate, two doors at the front
Approvals	
Approvals:	Bureau Veritas CSA DNV-GL

Lloyds Register of Shipping
RRR
Russian Maritime Register of Shipping
TÜV UL + C-UL

Certificates: EAC
IK-Code
Protection category
Protection category IP 55 (CPRI)

Declarations: Declaration of conformity
Manufacturer's declaration
