

Rittal – The System.

Faster – better – everywhere.

► Baying enclosure system VX25 Basic enclosure – VX 8208.000

Date : Nov 26, 2019

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Baying enclosure system VX25 Basic enclosure – VX 8208.000

created: 26.11.2019 on www.rittal.com/com-en



Product description

Material:	Enclosure frame: Sheet steel, 1.5 mm Roof: Sheet steel, 1.5 mm Door: Sheet steel, 2.0 mm Rear panel: Sheet steel, 1.5 mm Gland plates: Sheet steel, 1.5 mm Mounting plate: Sheet steel, 3.0 mm
Surface finish:	Enclosure frame: Dipcoat-primed Door, roof and rear panel: Dipcoat-primed, powder-coated on the outside, textured paint
Colour:	RAL 7035
Protection category IP to IEC 60 529:	IP 55
Protection category NEMA:	NEMA 12
Type rating to UL 508A:	Type 1, 12
IK Code:	IK10
Supply includes:	Enclosure frame Door(s) Door hinged on the right, may be swapped to the left Roof plate Rear panel Gland plates Mounting plate 2 punched rails 18 x 39 mm Lock: 3 mm double-bit

Basic material: Sheet steel

Product features

Dimensions: Width: 1200 mm
Height: 2000 mm
Depth: 800 mm

Mounting plate: Width: 1099 mm
Height: 1896 mm

Number of doors: 2

Packs of: 1 pc(s).

Weight/pack: 203 kg

EAN: 4028177813595

Customs tariff number: 94032080

ETIM 7.0: EC000261

ETIM 6.0: EC000261

eCl@ss 8.0/8.1: 27180101

eCl@ss 6.0/6.1: 27180101

Product description: VX Baying enclosure system, WHD: 1200x2000x800 mm, sheet steel, with mounting plate, two doors at the front

Approvals

Approvals: CSA
DNV-GL
Lloyds Register of Shipping
UL + C-UL

Certificates: EAC
Protection category

Declarations: Declaration of conformity