

# Rittal – The System.

Faster – better – everywhere.

## – TS 3313.100

Date : 2020.09.29

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# – TS 3313.100

created: 29.09.2020 build on [www.rittal.com/hr-hr](http://www.rittal.com/hr-hr)



## Product description

<b>Description:</b>	For laying, securing and storing cables or as an empty enclosure with uneven Liquid Cooling Package (LCP) installations.
<b>Benefits:</b>	Optimum accommodation of surplus cables and structured cable management
<b>Applications:</b>	As a cable management rack between fully configured network and server racks As an empty enclosure for symmetrical balancing in cold/hot aisle containment with an uneven number of LCPs in two enclosure suites As a placeholder for easy retrofitting of LCP installations
<b>Material:</b>	Čelični lim
<b>Surface finish:</b>	Enclosure frame: Dipcoat-primed Doors and roof: Dipcoat-primed, powder-coated
<b>Colour:</b>	Enclosure: RAL 7035 Front: RAL 9005
<b>Supply includes:</b>	Enclosure frame with front and rear door Aluminium door, front, solid with black designer trim panel, 180° hinges Sheet steel door at the rear, solid, 180° hinges Lock front and rear: Comfort handle for profile half-cylinders and security lock 3524 E 2 roof/base plates, with cut-outs for cable entry via brush strips 3 TS punched sections with mounting flanges mounted on the left and right Baying seal
<b>Note:</b>	For positioning at the start/end of an enclosure suite, a side panel will be required
<b>Basic material:</b>	Čelični lim

## Product features

<b>Dimensions:</b>	Width: 300 mm Height: 2000 mm Depth: 1000 mm
<b>Packs of:</b>	1 pc(s).
<b>Weight/pack:</b>	92 kg
<b>EAN:</b>	4028177708013
<b>Customs tariff number:</b>	94032080
<b>ETIM 7.0:</b>	EC000721
<b>ETIM 6.0:</b>	EC000721
<b>eCl@ss 8.0/8.1:</b>	27182003
<b>eCl@ss 6.0/6.1:</b>	27189270
<b>Product description:</b>	TS Cable management enclosure, WHD: 300 x 2000 x 1000 mm

## Approvals

<b>Certificates:</b>	EAC
<b>Declarations:</b>	Declaration of conformity