

TYPE APPROVAL CERTIFICATE

Certificate No: **TAE0000138** Revision No: **1**

This is to certify: That the Electric Bus Bar

with type designation(s) Busbar System Riline60, Busbar System Maxi-PLS, Busbar System Flat-PLS

Issued to Rittal GmbH & Co. KG Herborn, Hessen, Germany

is found to comply with DNV GL rules for classification – Ships and offshore units

Application : Product(s) approved by this certificate is/are accepted for installation on all vessels classed by DNV GL.

Issued at Hamburg on 2021-06-22

This Certificate is valid until **2026-06-21**. DNV local station: **Essen**

Approval Engineer: Harald Amberger

Arne Schaarmann Head of Section

LEGAL DISCLAIMER: Unless otherwise stated in the applicable contract with the holder of this document, or following from mandatory law, the liability of DNV AS, its parent companies and their subsidiaries as well as their officers, directors and employees ("DNV") arising from or in connection with the services rendered for the purpose of the issuance of this document or reliance thereon, whether in contract or in tort (including negligence), shall be limited to direct losses and under any circumstance be limited to 300,000 USD.



for **DNV**

This Certificate is subject to terms and conditions overleaf. Any significant change in design or construction may render this Certificate invalid. The validity date relates to the Type Approval Certificate and not to the approval of equipment/systems installed.



TAE0000138

1

Product description

Busbar System Riline60: Rated voltage Un: 690V AC, 1500V DC Rated frequency fn: 50Hz Rated insulation voltage Ui: 1000V Rated impulse withstand voltage Uimp: 8kV Rated current In (40°C): up to 1600A Rated peak withstand current Ipk: up to 105kA Rated short-time withstand current Icw: up to 50kA for 1s/3s	
Busbar supports: SV 9340.000/004/010/050 SV 9340.030/040 SV 9340.090 SV 3504/05/14/15.000	Busbar supports flat copper busbars Busbar support for flat copper bars, 1-/2-pole Spacers for RiLine busbar supports (flat busbar system) PLS busbar connectors
OM adapters / supports: SV 9340.260/270/300 SV 9340.760 SV 9340.310/320/340/370 SV 9340.400 SV 9340.350/380/390/770 SV 9340.460/470 SV 9340.710 - 750 SV 9340.710 - 750 SV 9340.510 - 560/660 SV 9340.610 - 650 SV 9340.900 - 930	OM supports without contact system OM adaptors with connection cables, 3-pole, 16A OM adaptors with connection cables, 3-pole, 25A, width 45mm OM adaptors with connection cables, 3-pole, 25A, width 90mm OM adaptors with connection cables, 3-pole, 32A, width 45mm OM adaptors with connection cables, 3-pole, 32A, width 55mm OM adaptors with connection cables, 3-pole, 40A OM adaptors with connection cables, 3-pole, 40A OM adaptors with connection cables, 3-pole, 65A OM adaptors with tension spring clamp, 3-pole, 32A OM adaptors with tension spring clamp, 3-pole, 65A OM adaptors with plug-in cable outlet, 3pole, 25A
Connection adaptors / block: SV 9342.200/210 SV 9342.220/240 SV 9342.250/270 SV 9342.280/300 SV 9342.224 SV 9342.254 SV 9342.310/314 SV 9342.320/324 SV 9342.311/321	Connection adaptors, 3-pole, 63A Connection adaptors, 3-pole, 125A Connection adaptors, 3-pole, 250A Connection adaptors, 3-pole, 800A Connection adaptors, 4-pole, 125A Connection adaptors, 4-pole, 250A Connection adaptors, 3-pole, expansion set for 4-pole, 800A Connection adaptors, 3-pole, expansion set for 4-pole, 1600A Connection block, 1-pole, 800A, 1600A
Circuit-breaker component adapto SV 9342.400/410 SV 9342.540/550 SV 9342.500/510 SV 9345.600/610 SV 9345.720/730 SV 9345.700/710 SV 9345.700/710 SV 9342.504/514 SV 9345.604/614 Bus-mounting fuse bases SV 3418.010/040 SV 3427.010/040	Circuit-breaker component adaptors, 3-pole, 100A Circuit-breaker component adaptors, 3-pole, 125A Circuit-breaker component adaptors, 3-pole, 160A Circuit-breaker component adaptors, 3-pole, 250A Circuit-breaker component adaptors, 3-pole, 400A Circuit-breaker component adaptors, 3-pole, 630A Circuit-breaker component adaptors, 4-pole, 160A Circuit-breaker component adaptors, 4-pole, 250A Bus-mounting fuse bases, D 02-E 18, 63A Bus-mounting fuse bases, D 11-E 27, 25A
SV 3433.010/040	Bus-mounting fuse bases, D III-E 33, 63A



TAE0000138

Hardware busbar system Maxi-PLS:

Rated voltage U_n: 690 V AC, 1000 V DC Rated frequency f_n: 50 Hz Rated insulation voltage U_i: 1000V Rated impulse withstand voltage U_{imp}: 8 kV Rated current I_n (40° C): up to 4000A Rated peak withstand current I_{pk}: up to 154kA Rated short-time withstand current I_{cw}: up to 70kA for 1s

Busbar supports:

SV 9649.000/9659.000Busbar supportSV 9649.160/9659.160Busbar support, suitable for top mountingSV 9649.010/9659.010End support

Hardware busbar system Flat-PLS:

Rated voltage U_n : 690 V AC, 1500V DC Rated frequency f_n : 50 Hz Rated insulation voltage U_i : 1000V Rated impulse withstand voltage U_{imp} : 12 kV Rated current I_n (40°C): up to 5500A Rated peak withstand current I_{pk} : up to 220kA Rated short-time withstand current I_{cw} : up to 100kA for 1s

Busbar supports:SV 9676.002/004Busbar support Flat-PLSSV 9676.020/021Busbar support for stabiliser barSV 9676.503/504/505Spacer rolls for Maxi PLS busbar and flat copper barsSV 9676.621/641Longitudinal connectorsSV 9676.700/710Connection plates with studsSV 9676.007/008Spacers and filler pieces

Application/Limitation

Location classes / Test: Insulation resistance test:500 VDC, Test A 100 MOhm, Test B 10 MOhm High voltage test: 2000 VAC, 50 Hz Performance test: IEC60439-1, IEC61439-2 Vibration: Location classes A

Type Approval documentation

U145928E1, U145928E2 1579.0522.1.318e, 1579.0797.5.292d, 1579.0797.5.293e, 1579.0797.5.294e 1579.0930.6.858e, 1579.0930.6.862e, 1579.0948.6.867e, 1579.2080837.420, 1579.2080904.435e 1579.2081382.1180e, 1579.2081382.1181e 2012-00139e, 2012-00204e, 2012-00206e ASTA_16700, ASTA_16701, ASTA_16940, ASTA_16942, ASTA_16943, ASTA_16945, ASTA_17110 ASTA_17111, ASTA_17112, ASTA_17151, ASTA_17163, ASTA_17165, ASTA_17166, ASTA_17230 ASTA_17603, ASTA_17604, ASTA_17744, ASTA_17745, ASTA_17917, ASTA_17918, ASTA_19629 ASTA_19630, ASTA_20105 TR 8000--231-001e, TR 8000--231-002e, TR 8000--231-004e, TR 8000--231-005e, TR 8000--231-008e TR 8000--231-010e Brochure Technical System Catalogue Ri4Power Brochure Technical System Catalogue Ri4Power Brochure Technical System Catalogue RiLine60 Technical details - 2nd edition 2015, pages 2-100 to 2-129 General Instruction rules for Power distribution solutions of Rittal.doc



Job Id: Certificate No: **TAE0000138** Revision No: **1**

Tests carried out

Test standard acc.: Environmental tests acc. DNVGL-CG-0339 IEC 61439-2012, DIN EN 61439-2012

Marking of product

Rittal, manufacturing place and type number.

Periodical assessment

The scope of the periodical assessment is to verify that the conditions stipulated for the Type approval are complied with and that no alterations are made to the product design or choice of materials.

The main elements of the assessment are:

- Inspection on factory samples, selected at random from the production line (where practicable)
- Results from Routine Tests (RT) checked (if not available tests according to RT to be carried out)
- Review of type approval documentation
- Review of possible change in design, materials and performance
- Ensuring traceability between manufacturer's product type marking and Type Approval Certificate.

Periodical assessment is to be performed after 2 years and after 3.5 years. A renewal assessment will be performed at renewal of the certificate.

END OF CERTIFICATE