



Ref. Certif. No.

**DK-168169-UL**

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

**CB TEST CERTIFICATE**

|                                                                           |                                                                                                                                                                                       |
|---------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Product                                                                   | Liquid Chiller                                                                                                                                                                        |
| Name and address of the applicant                                         | RITTAL GmbH & Co. KG<br>Auf Dem Stutzelberg 1 Herborn 35745<br>Germany                                                                                                                |
| Name and address of the manufacturer                                      | RITTAL GmbH & Co. KG<br>Auf Dem Stutzelberg 1 Herborn 35745<br>Germany                                                                                                                |
| Name and address of the factory                                           | Rittal RCS Cooling Solutions S.r.l.<br>VIA DEGLI IMPRENDITORI 15 VALEGGIO SUL MINCIO, VR, 37067<br>Italy<br><input type="checkbox"/> <a href="#">Additional Information on page 2</a> |
| Note: When more than one factory, please report on page 2                 |                                                                                                                                                                                       |
| Ratings and principal characteristics                                     | SK 3319100<br>380 – 415 V, 3~, 50 Hz, 1050 W<br>R513a, 550 g, HP: 25 bar, LP: 16 bar<br><input checked="" type="checkbox"/> <a href="#">Additional Information on page 2</a>          |
| Trademark / Brand (if any)                                                |                                                                                                     |
| Customer's Testing Facility (CTF) Stage used                              | CTF Stage 1                                                                                                                                                                           |
| Model / Type Ref.                                                         | SK 3319100, SK 3320200, SK 3334300, SK 3334400 and SK 3334450                                                                                                                         |
| Additional information (if necessary may also be reported on page 2)      | National Differences: EU Group Differences, DK, FI, NO, SE, GB<br><input checked="" type="checkbox"/> <a href="#">Additional Information on page 2</a>                                |
| A sample of the product was tested and found to be in conformity with     | IEC 60335-1:2010, IEC 60335-1:2010/AMD1:2013, IEC 60335-1:2010/AMD2:2016, IEC 60335-2-40:2022                                                                                         |
| As shown in the Test Report Ref. No. which forms part of this Certificate | 25-4791215515.1 issued on 2025-06-23                                                                                                                                                  |

This CB Test Certificate is issued by the National Certification Body



- ☐ UL Solutions (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- ☒ UL Solutions (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- ☐ UL Solutions (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- ☐ UL Solutions (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see [www.ul.com/ncbnames](http://www.ul.com/ncbnames)

Date: 2025-06-27

Signature:  
Thomas Wilson



Ref. Certif. No.

**DK-168169-UL**

**Additional Ratings:**

SK 3320200:

380 – 415 V, 3~, 50 Hz, 1350 W

R513a, 650 g, HP: 25 bar, LP: 16 bar

SK 3334300:

380 – 415 V, 3~, 50 Hz, 2630 W

R513a, 700 g, HP: 25 bar, LP: 16 bar

SK 3334400:

380 – 415 V, 3~, 50 Hz, 2630 W

R513a, 1200 g, HP: 25 bar, LP: 16 bar

SK 3334450:

380 – 415 V, 3~, 50 Hz, 2840 W

R513a, 1500 g, HP: 25 bar, LP: 16 bar

**Additionally evaluated to:**

EN 60335-1:2012, EN 60335-1:2012/A11:2014, EN 60335-1:2012/A13:2017, EN 60335-1:2012/A1:2019, EN 60335-1:2012/A2:2019, EN 60335-1:2012/A14:2019, EN 60335-1:2012/A15:2021, EN 60335-1:2012/A16:2023, EN IEC 60335-2-40:2023, EN IEC 60335-2-40:2023/A11:2023, EN 62233:2008

**Additional information (if necessary)**



- ☐ UL Solutions (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- ☒ UL Solutions (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- ☐ UL Solutions (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- ☐ UL Solutions (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see [www.ul.com/ncbnames](http://www.ul.com/ncbnames)

Date: 2025-06-27

Signature:

Thomas Wilson