



C30202 PDU/CABLE MAN. BRK RAL90105 PART No.: 438182				COPYRIGHT OF THIS DRAWING IS RESERVED BY RITTAL-CSM LTD. IT IS ISSUED ON CONDITION THAT IT IS NOT REPRODUCED, COPIED, OR DISCLOSED TO A THIRD PARTY EITHER WHOLLY OR IN PART WITHOUT THE CONSENT IN WRITING OF RITTAL-CSM LTD.		ALPHABETICAL DRAWING ISSUES ARE NOT ISSUE CONTROLLED AND ARE USED FOR MANUFACTURE OF SPECIALS AND PROTOTYPES. ONLY NUMERICAL DRAWING ISSUES ARE TO BE USED FOR STANDARDS AND ARE ISSUE CONTROLLED.		TOLERANCE UNLESS OTHERWISE STATED ANSI STANDARD: 0.0 : ±0.8 0.00 : ±0.5 0.000 : ±0.25 ANGLES : ±1.0°		SCALE 1.00 @ A3 R.F.E.A No. 0	
ITEM DESCRIPTION QTY PART NO. DWG NO.				DATE DD/MM/YY NAME		DRN 29/07/20 M.S.		MASS APPROX. 3.18 Kg		MATERIAL MILD STEEL DC01, 1.2mm THK	
2 PDU/CABLE MAN. BRK. 48U, 1 438183 C30202				6 E.C.N. 9214 11/05/21 DG		C.		DESCRIPTION TS-IT RITTAL		DWG No C30202 6	
3 PAINT: - RAL9005 2 PART DIP MIX 0.039 kg 478517 478517				5 E.C.N. 9214 04/12/20 DG		I.S.		ALL INSIDE BEND RADII ARE 1-1.5 x MAT'L THICKNESS FOLDS 90° UNLESS OTHERWISE STATED ALL DIMENSIONS TYPICAL UNLESS OTHERWISE STATED		PART NO. 438182- RITTAL-CSM, UK.	
1 ECN 9214 21/09/20 MS				3 E.C.N. 9214 29/09/20 I.S.		MS		ALL PARTS TO BE COMPLIANT TO: AA-TL035		(CRITICAL DIMENSION)	
A DRAWN 30/07/20 MS				ISS. E.C.N. No / DESCRIPT. DATE NAME		RITTAL		THIRD ANGLE PROJECTION. REMOVE ALL BURRS AND SHARP EDGES. ALL DIM'S ARE IN MM		1 OF 2	



SCALE 0.150



SCALE 0.150

FLAT BLANK
FOR REFERENCE ONLY

SCALE	0.50 @ A3	R.F.E.A. 0
MATERIAL	MILD STEEL DC01, 1.2mm THK	
DESCRIPTION	TS-IT	RITTAL
	PDU/CABLE MAN. BRK. 48U,	
DWG No	C30202	ISS. 6
DRAWING SHEET 2 OF 2		