



Ref. Certif. No.

DK-183614-UL

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Water to Air Heat Exchangers for IT Equipment Hydronic fan coil for IT equipment cooling

Name and address of the applicant

RITTAL GmbH & Co. KG
Auf Dem Stutzelberg Herborn 35745
Germany

Name and address of the manufacturer

RITTAL GmbH & Co. KG
Auf Dem Stutzelberg Herborn 35745
Germany

Name and address of the factory

KELVIN SRL
VIA DEGLI IMPRENDITORI 15
VALEGGIO SUL MINCIO VR 37067
Italy

Note: When more than one factory, please report on page 2

☐ [Additional Information on page 2](#)

Ratings and principal characteristics

90-264 V ~, 50/60 Hz, 0.5 kW, 10°C - 50°C, IP20

Trademark / Brand (if any)



Customer's Testing Facility (CTF) Stage used

Model / Type Ref.

SK 3313610

Additional information (if necessary may also be reported on page 2)

Evaluated to National or Group Differences for EU Group Differences, AU, JP, NZ

☒ [Additional Information on page 2](#)

A sample of the product was tested and found to be in conformity with

IEC 60335-2-40:2018, IEC 60335-1:2010, IEC 60335-1:2010/AMD1:2013, IEC 60335-1:2010/AMD2:2016

As shown in the Test Report Ref. No. which forms part of this Certificate

4792255207.2 issued on 2026-07-31

This CB Test Certificate is issued by the National Certification Body



- ☐ UL Solutions (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- ☒ UL Solutions (Denmark), Borupvang 5A DK-2750 Ballerup, DENMARK
- ☐ UL Solutions (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- ☐ UL Solutions (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/nbnames

Date: 2026-08-03

Signature:

Thomas Wilson



Ref. Certif. No.

DK-183614-UL

Evaluated to National Differences declared for:

EN IEC 60335-2-40:2023, EN IEC 60335-2-40:2023/A11:2023, EN 60335-1:2012, EN 60335-1:2012/A11:2014,
EN 60335-1:2012/A13:2017, EN 60335-1:2012/A1:2019, EN 60335-1:2012/A14:2019, EN 60335-1:2012/A2:2019,
EN 60335-1:2012/A15:2021, EN 60335-1:2012/A16:2023, EN 62233:2008

Additional information (if necessary)



- ☐ UL Solutions (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- ☒ UL Solutions (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- ☐ UL Solutions (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- ☐ UL Solutions (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2026-08-03

Signature:

Thomas Wilson