

# 11 Technical specifications

EN

<b>Technical specifications</b>	
Description/Model No.	Condenser / 9951.077
<b>Dimensions and weights</b>	Horizontal
Dimensions width x height x depth [in]	69.8 x 45.6 x 18.1
Weight, operating [lb]	164
Weight, shipping [lb]	233
<b>Electrical connection</b>	
Rated voltage [V, Hz]	208/230, 1~, 60
Voltage range [V]	187...253
Fan quantity	2
Power/Fan [HP]	1/8
Full load amps [A]	3.2
Minimum circuit amps [A]	15
Maximum overcurrent protective device [A]	15
<b>Cooling circuit</b>	
Refrigerant	R-410a
External diameter of refrigerant lines [in]	1 1/8 (gas), 7/8 (liquid)
<b>Other information</b>	
Ambient temperature [°C] (°F)	-29...+38 ±6 (-20...+100 ±10)

Tab. 14: Technical specifications for the condenser unit (for operation with 3311.415/425/435/445)