


Stainless steel Catalogue 33, page 195



Model No. SE		Width dimensions mm									Height dimensions mm								Depth dimensions mm						Mounting plates mm	
Spray-finished	Stainless steel	B1	B2	B3	B4	B5	B6	B7	B8	B9	H1	H2	H3	H4	H5	H6	H7	H8	T1	T2	T3	T4	T5	T6	F	G
5830.500	—	600	592	512	592	475	455	475	535	440	1800	1797	1712	1777.5	1675	1650	1630	910	405	275	312	240	324	126.5 — 356.5	499	1696
5831.500	—	800	792	712	792	675	655	675	735	640	1800	1797	1712	1777.5	1675	1650	1630	910	405	275	312	240	324	126.5 — 356.5	699	1696
5832.500	—	800	792	712	792	675	655	675	735	640	2000	1997	1912	1977.5	1875	1850	1830	1010	405	275	312	240	324	126.5 — 456.5	699	1896
5833.500	—	800	792	712	792	675	655	675	735	640	2000	1997	1912	1977.5	1875	1850	1830	1010	505	375	412	340	424	126.5 — 456.5	699	1896
5834.500	5853.500	800	792	712	792	675	655	675	735	640	2000	1997	1912	1977.5	1875	1850	1830	1010	605	475	512	440	524	126.5 — 556.5	699	1896
—	5850.500	600	592	512	592	475	455	475	535	440	1600	1597	1512	1577.5	1475	1450	1430	810	405	275	312	240	324	126.5 — 356.5	499	1496
—	5851.500	600	592	512	592	475	455	475	535	440	1800	1797	1712	1777.5	1675	1650	1630	910	505	375	412	340	424	126.5 — 456.5	499	1696
—	5852.500	800	792	712	792	675	655	675	735	640	1800	1797	1712	1777.5	1675	1650	1630	910	505	375	412	340	424	126.5 — 456.5	699	1696
—	5854.500	1000	992	912	992	875	855	875	935	400	1800	1797	1712	1777.5	1675	1650	1630	910	405	275	312	240	324	126.5 — 356.5	899	1696

Enclosures


Enclosure systems

System enclosure SE 8

Spray-finished Catalogue 33, page 98

Stainless steel Catalogue 33, page 195

Mounting plate




Enclosure

- B1 = Overall width
- B2 = Width of door
- B3 = Clearance of enclosure frame
- B5 = Section length of system punchings/
hole spacing base/plinth attachment
- B6 = Clearance of tubular door frame
- B7 = Distance between axes of tubular door
frame holes
- B8 = Distance between the lifting eyes
- B9 = Clearance in the base opening
- H1 = Overall height
- H2 = Height of rear panel
- H3 = Clearance of enclosure frame
- H4 = Height of door
- H5 = Section length of system punchings
- H6 = Distance between axes of tubular door
frame holes
- H7 = Clearance of tubular door frame
- H8 = Distance from base to centre of lock
- T1 = Overall depth
- T2 = Section length of system punchings/
hole spacing base/plinth attachment
- T3 = Clearance of enclosure frame
- T4 = Clearance of base opening
- T5 = Centre of lifting eye to centre of lifting eye
- T6 = Possible mounting depth (mounting plate
assembly) up to 149 mm depth-adjustable
on a 25 mm pitch pattern


Mounting plate

- F = Overall width
- G = Overall height


Cross-section




Pitch pattern of holes



Enclosure corner top



Enclosure corner bottom



- 1 Width
- 2 Height
- 3 Depth

Double-door

Model No. SE		Width dimensions mm									Height dimensions mm								Depth dimensions mm						Mounting plates mm	
Spray-finished	Stainless steel	B1	B2	B3	B4	B5	B6	B7	B8	B9	H1	H2	H3	H4	H5	H6	H7	H8	T1	T2	T3	T4	T5	T6	F	G
5840.500	—	1000	492	912	992	875	355	375	935	400	1800	1797	1712	1777.5	1675	1650	1630	910	405	275	312	240	324	126.5	899	1696
5841.500	—	1200	592	1112	1192	1075	455	475	1135	500	1800	1797	1712	1777.5	1675	1650	1630	910	405	275	312	240	324	—	1099	1696
5842.500	—	1600	792	1512	792	1475	655	675	1535	690	1800	1797	1712	1777.5	1675	1650	1630	910	405	275	312	240	324	356.5	1499	1696
5843.500	—	1200	592	1112	1192	1075	455	475	1135	500	2000	1997	1912	1977.5	1875	1850	1830	1010	405	275	312	240	324	—	1099	1896
5844.500	5855.500	1200	592	1112	1192	1075	455	475	1135	500	2000	1997	1912	1977.5	1875	1850	1830	1010	505	375	412	340	424	126.5 — 456.5	1099	1896
5845.500	—	1200	592	1112	1192	1075	455	475	1135	500	2000	1997	1912	1977.5	1875	1850	1830	1010	605	475	512	440	524	126.5	1099	1896
5846.500	—	1800	892	1712	892	1675	755	775	1735	790	2000	1997	1912	1977.5	1875	1850	1830	1010	505	375	412	340	424	— 556.5	1699	1896