

Enclosures


PC enclosure systems

PC enclosure systems


with keyboard drawer

With glazed door and drawer

PC 5366.050, PC 5368.050, PC 5386.050





i.L. = Clearance width





- 1 Max. 505, adjustable on a 25 mm pitch pattern
- 2 Max. 547, adjustable on a 25 mm pitch pattern

With mounting compartment, small and drawer
PC 5366.350




- 1 Max. 355, adjustable on a 25 mm pitch pattern
- 2 Max. 397, adjustable on a 25 mm pitch pattern

With mounting compartment, large and drawer
PC 5366.450



View X




		Dimensions width x depth mm		Model No. PC		
		600 x 636		5366.050	5366.350	5366.450
		600 x 836		5368.050	—	—
		800 x 636		5386.050	—	—
Scope of supply	Design	Material	Colour RAL			
Enclosure	Enclosure structure with one-piece side panels and roof	Sheet steel, 1.5 mm	7035 textured	■	■	■
	Gland plates, three-part (5368.000, four-part)	Sheet steel, 1.5 mm	Zinc-plated			
Rear door	With locking rod and double-bit insert, r/h hinge	Sheet steel, 2.0 mm	7035 textured	■	■	■
Glazed door, top	With support frame latched from the inside ¹⁾ , r/h hinge	Sheet steel, 1.5 mm	7015	■	■	—
	Vertical decorative trim panels	Plastic to UL 94-V0	7035			
	Pane with screen-printed mask	Toughened safety glass 4.0 mm	7015			
Mounting compartment, large, top	Vertical bars, latched from the inside ¹⁾ , hinged on r/h side	Aluminium section	7035	—	—	■
	Installation plate	Sheet steel, 1.5 mm	7015			
	Trim strip top/bottom	Plastic to UL 94-V0	7035			
Component shelf for monitor	Slotted, permanently installed	Sheet steel, 1.5 mm	7015	■	■	—
Drawer for keyboard	Enclosure	Sheet steel, 1.5 mm	7035	■	■	■
	Keyboard extension piece with cable support, pull-out mousepad and keyboard cradle	Sheet steel, 1.5 mm	7035			
	Trim panel with handle strip, folded as handrest, with lock no. 3524 E	Plastic to UL 94-V0	7035/7015/9006			
Mounting compartment, small	R/h hinge, screw-fastened from the inside on the left, folded mounting plate	Sheet steel, 1.5 mm	7015	—	■	—
	Decorative side trim panels	Plastic to UL 94-V0	7035			
Bottom door	Vertical bars with locking rod and double-bit insert, hinged on r/h side	Aluminium section	7035	■	■	■
	Door or installation plate folded	Sheet steel, 1.5 mm	7015			

¹⁾ With unlatching for top glazed door


with folding keyboard or desk section

With glazed door and desk section
PC 5366.250



- 1 Max. 505, adjustable on a 25 mm pitch pattern
- 2 Max. 547, adjustable on a 25 mm pitch pattern
- 3 Max. installation surface 540 x 175 mm

View X



				Model No. PC		
				Depth 636 mm	5366.150	5366.250
Scope of supply	Design	Material	Colour RAL			
Enclosure	Enclosure structure with one-piece side panels and roof	Sheet steel, 1.5 mm	7035 textured	■	■	
	Gland plates, three-part	Sheet steel, 1.5 mm	Zinc-plated			
Rear door	With locking rod and double-bit insert, r/h hinge	Sheet steel, 2.0 mm	7035 textured	■	■	
Glazed door, top	With support frame latched from the inside ¹⁾ , r/h hinge	Sheet steel, 1.5 mm	7015	■	■	
	Vertical decorative trim panels	Plastic to UL 94-V0	7035			
	Pane with screen-printed mask	Toughened safety glass 4.0 mm	7015			
Component shelf for monitor	Slotted, permanently installed	Sheet steel, 1.5 mm	7015	■	■	
Fold-out tray for keyboard	Enclosure with mouse support and cut-out in the rear panel, width 482.6 mm (19") x height 4 HE, for rear attachment	Sheet steel, 1.5 mm	7035	■	—	
	Trim panel hinged at the bottom, with 2 retaining cords, with lock no. 3524 E	Plastic to UL 94-V0	7035/7015/9006			
	Keyboard support with mousepad extension piece and 2 nylon loop tapes for keyboard	Sheet steel, 1.5 mm	7035			
Desk section	Enclosure with removable cover top and bottom	Sheet steel 1.5 mm/2.0 mm	7035	—	■	
	Trim strip, top and handle strip	Plastic to UL 94-V0	7035/7015/9006			
Bottom door	Vertical bars with locking rod and double-bit insert, hinged on r/h side	Aluminium section	7035	■	■	
	Door or installation plate folded	Sheet steel, 1.5 mm	7015			

¹⁾ With unlatching for top glazed door