

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 22.11.2022

Version number 13 (replaces version 12)

Revision: 22.11.2022

SECTION 1: Identification of the substance/mixture and of the company/undertaking

- **1.1 Product identifier**
- **Trade name: Rittal Decklack**
- **1.2 Relevant identified uses of the substance or mixture and uses advised against**
No further relevant information available.
- **Application of the substance / the mixture** Paint
- **1.3 Details of the supplier of the safety data sheet**
- **Manufacturer/Supplier:**
RITTAL GmbH & Co.KG
Auf dem Stützelberg
D-35745 Herborn
Phone: +49 2772 505 0
e-mail: info@rittal.de
- **1.4 Emergency telephone number:**
Informationszentrale gegen Vergiftungen Bonn
Tel.: 0228/19240 (emergency)
0228/287-3-3480 (office)
Fax: 0228/287-3-3278

SECTION 2: Hazards identification

- **2.1 Classification of the substance or mixture**
- **Classification according to Regulation (EC) No 1272/2008**



flame

Flam. Liq. 3 H226 Flammable liquid and vapour.



health hazard

STOT RE 2 H373 May cause damage to organs through prolonged or repeated exposure.



environment

Aquatic Chronic 2 H411 Toxic to aquatic life with long lasting effects.



Skin Irrit. 2 H315 Causes skin irritation.
 Eye Irrit. 2 H319 Causes serious eye irritation.
 Skin Sens. 1 H317 May cause an allergic skin reaction.
 STOT SE 3 H335-H336 May cause respiratory irritation. May cause drowsiness or dizziness.

(Contd. on page 2)

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 22.11.2022

Version number 13 (replaces version 12)

Revision: 22.11.2022

Trade name: Rittal Decklack

(Contd. of page 1)

- **2.2 Label elements**
- **Labelling according to Regulation (EC) No 1272/2008**
The product is classified and labelled according to the GB CLP regulation.
- **Hazard pictograms** GHS02, GHS07, GHS08, GHS09
- **Signal word** Warning
- **Hazard-determining components of labelling:**
Hydrocarbons, C9, aromatics
Xylene
2-Methoxy-1-methylethyl acetate
Reaction mass of pentamethyl-piperidyl sebacate
- **Hazard statements**
H226 Flammable liquid and vapour.
H315 Causes skin irritation.
H319 Causes serious eye irritation.
H317 May cause an allergic skin reaction.
H335-H336 May cause respiratory irritation. May cause drowsiness or dizziness.
H373 May cause damage to organs through prolonged or repeated exposure.
H411 Toxic to aquatic life with long lasting effects.
- **Precautionary statements**
P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
P260 Do not breathe dust/fume/gas/mist/vapours/spray.
P280 Wear protective gloves/protective clothing/eye protection/face protection/hearing protection.
P303+P361+P353 IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water [or shower].
P304+P340 IF INHALED: Remove person to fresh air and keep comfortable for breathing.
P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
- **2.3 Other hazards**
- **Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.

SECTION 3: Composition/information on ingredients

- **3.2 Mixtures**
- **Description:** Mixture of substances listed below with nonhazardous additions.

- **Dangerous components:**

CAS: 64742-95-6 EC number: 918-668-5 Reg.nr.: 01-2119455851-35	Hydrocarbons, C9, aromatics ⚠ Flam. Liq. 3, H226; ⚠ Asp. Tox. 1, H304; ⚠ Aquatic Chronic 2, H411; ⚠ STOT SE 3, H335-H336, EUH066	25-50%
CAS: 1330-20-7 EINECS: 215-535-7 Reg.nr.: 01-2119488216-32	Xylene ⚠ Flam. Liq. 3, H226; ⚠ STOT RE 2, H373; Asp. Tox. 1, H304; ⚠ Acute Tox. 4, H312; Acute Tox. 4, H332; Skin Irrit. 2, H315; Eye Irrit. 2, H319; STOT SE 3, H335	≥10-≤20%
CAS: 100-41-4 EINECS: 202-849-4 Reg.nr.: 01-2119489370-35	Ethylbenzene ⚠ Flam. Liq. 2, H225; ⚠ STOT RE 2, H373; Asp. Tox. 1, H304; ⚠ Acute Tox. 4, H332; Skin Irrit. 2, H315; Eye Irrit. 2, H319; Aquatic Chronic 3, H412	2.5-<10%

(Contd. on page 3)

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 22.11.2022

Version number 13 (replaces version 12)

Revision: 22.11.2022

Trade name: Rittal Decklack

		(Contd. of page 2)
CAS: 108-65-6 EINECS: 203-603-9 Reg.nr.: 01-2119475791-29	2-Methoxy-1-methylethyl acetate ⚠ Flam. Liq. 3, H226; ⚠ STOT SE 3, H336	2.5-<10%
CAS: 112-07-2 EINECS: 203-933-3 Reg.nr.: 01-2119475112-47	2-Butoxyethyl acetate ⚠ Acute Tox. 4, H302; Acute Tox. 4, H312; Acute Tox. 4, H332	1-<2.5%
EC number: 915-687-0 Reg.nr.: 01-2119491304-40	Reaction mass of pentamethyl-piperidyl sebacate ⚠ Repr. 2, H361f; ⚠ Aquatic Acute 1, H400; Aquatic Chronic 1, H410; ⚠ Skin Sens. 1A, H317	≥0.25-<1%
CAS: 108-88-3 EINECS: 203-625-9 Reg.nr.: 01-2119471310-51	Toluene ⚠ Flam. Liq. 2, H225; ⚠ Repr. 2, H361d; STOT RE 2, H373; Asp. Tox. 1, H304; ⚠ Skin Irrit. 2, H315; STOT SE 3, H336	<1%

· **Additional information:** For the wording of the listed hazard phrases refer to section 16.

SECTION 4: First aid measures

- **4.1 Description of first aid measures**
- **General information:** Immediately remove any clothing soiled by the product.
- **After inhalation:**
Supply fresh air and to be sure call for a doctor.
In case of unconsciousness place patient stably in side position for transportation.
- **After skin contact:** Immediately rinse with water.
- **After eye contact:**
Rinse opened eye for several minutes under running water. If symptoms persist, consult a doctor.
- **After swallowing:** If symptoms persist consult doctor.
- **4.3 Indication of any immediate medical attention and special treatment needed**
No further relevant information available.

SECTION 5: Firefighting measures

- **5.1 Extinguishing media**
- **Suitable extinguishing agents:**
CO₂, powder or water spray. Fight larger fires with water spray or alcohol resistant foam.
- **For safety reasons unsuitable extinguishing agents:** Water with full jet
- **5.2 Special hazards arising from the substance or mixture**
During heating or in case of fire poisonous gases are produced.
- **5.3 Advice for firefighters**
- **Protective equipment:** Mouth respiratory protective device.

SECTION 6: Accidental release measures

- **6.1 Personal precautions, protective equipment and emergency procedures**
Mount respiratory protective device.
Wear protective equipment. Keep unprotected persons away.
- **6.2 Environmental precautions:**
Do not allow product to reach sewage system or any water course.
Inform respective authorities in case of seepage into water course or sewage system.
Do not allow to enter sewers/ surface or ground water.

(Contd. on page 4)

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 22.11.2022

Version number 13 (replaces version 12)

Revision: 22.11.2022

Trade name: Rittal Decklack

(Contd. of page 3)

- **6.3 Methods and material for containment and cleaning up:**
Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders, sawdust).
Dispose contaminated material as waste according to item 13.
Ensure adequate ventilation.
- **6.4 Reference to other sections**
See Section 7 for information on safe handling.
See Section 8 for information on personal protection equipment.
See Section 13 for disposal information.

SECTION 7: Handling and storage

- **7.1 Precautions for safe handling**
Ensure good ventilation/exhaustion at the workplace.
Prevent formation of aerosols.
- **Information about fire - and explosion protection:**
Keep ignition sources away - Do not smoke.
Protect against electrostatic charges.
Keep respiratory protective device available.
- **7.2 Conditions for safe storage, including any incompatibilities**
- **Storage:**
- **Requirements to be met by storerooms and receptacles:** No special requirements.
- **Information about storage in one common storage facility:** Store away from foodstuffs.
- **Further information about storage conditions:** Keep container tightly sealed.
- **Storage class:** 3
- **7.3 Specific end use(s)** No further relevant information available.

SECTION 8: Exposure controls/personal protection

8.1 Control parameters

Ingredients with limit values that require monitoring at the workplace:

1330-20-7 Xylene

WEL	Short-term value: 441 mg/m ³ , 100 ppm Long-term value: 220 mg/m ³ , 50 ppm Sk; BMGV
-----	--

100-41-4 Ethylbenzene

WEL	Short-term value: 552 mg/m ³ , 125 ppm Long-term value: 441 mg/m ³ , 100 ppm Sk
-----	---

108-65-6 2-Methoxy-1-methylethyl acetate

WEL	Short-term value: 548 mg/m ³ , 100 ppm Long-term value: 274 mg/m ³ , 50 ppm Sk
-----	--

112-07-2 2-Butoxyethyl acetate

WEL	Short-term value: 332 mg/m ³ , 50 ppm Long-term value: 133 mg/m ³ , 20 ppm Sk
-----	---

(Contd. on page 5)

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 22.11.2022

Version number 13 (replaces version 12)

Revision: 22.11.2022

Trade name: Rittal Decklack

(Contd. of page 4)

108-88-3 Toluene

WEL	Short-term value: 384 mg/m ³ , 100 ppm Long-term value: 191 mg/m ³ , 50 ppm Sk
-----	--

· **Ingredients with biological limit values:**

1330-20-7 Xylene

BMGV	650 mmol/mol creatinine Medium: urine Sampling time: post shift Parameter: methyl hippuric acid
------	--

· **Additional information:** The lists valid during the making were used as basis.

· **8.2 Exposure controls**

· **Appropriate engineering controls** No further data; see item 7.

· **Individual protection measures, such as personal protective equipment**

· **General protective and hygienic measures:**

Keep away from foodstuffs, beverages and feed.

Immediately remove all soiled and contaminated clothing

Wash hands before breaks and at the end of work.

Store protective clothing separately.

Avoid contact with the eyes.

Avoid contact with the eyes and skin.

· **Respiratory protection:**



In case of brief exposure or low pollution use respiratory filter device. In case of intensive or longer exposure use self-contained respiratory protective device.

· **Hand protection**

Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation



Protective gloves (EN 374)

The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.

· **Material of gloves**

The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked prior to the application.

· **Breakthrough time of glove material**

The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.

(Contd. on page 6)

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 22.11.2022

Version number 13 (replaces version 12)

Revision: 22.11.2022

Trade name: Rittal Decklack

(Contd. of page 5)

· **Eye/face protection**



Tightly sealed goggles

SECTION 9: Physical and chemical properties

· **9.1 Information on basic physical and chemical properties**

· **General Information**

· **Physical state**

Fluid

· **Colour:**

According to product specification

· **Odour:**

Characteristic

· **Odour threshold:**

Not determined.

· **Melting point/freezing point:**

Undetermined.

· **Boiling point or initial boiling point and boiling range**

137-143 °C (1330-20-7 Xylene)

· **Flammability**

Flammable.

· **Lower and upper explosion limit**

· **Lower:**

0.7 Vol %

· **Upper:**

7.5 Vol %

· **Flash point:**

24 °C (DIN EN ISO 1523:2002)

· **Ignition temperature:**

450 °C (DIN 51794)

· **Decomposition temperature:**

Not determined.

· **pH**

Not determined.

· **Viscosity:**

· **Kinematic viscosity at 20 °C**

160-180 s (DIN 53211/4)

· **Dynamic:**

Not determined.

· **Solubility**

· **water:**

Not miscible or difficult to mix.

· **Partition coefficient n-octanol/water (log value)**

Not determined.

· **Vapour pressure at 20 °C:**

6.7-8.2 hPa

· **Density and/or relative density**

· **Density at 20 °C:**

1.037 g/cm³ (DIN EN ISO 2811-1)

· **Relative density**

Not determined.

· **Vapour density**

Not determined.

· **9.2 Other information**

· **Appearance:**

· **Form:**

Fluid

· **Important information on protection of health and environment, and on safety.**

· **Auto-ignition temperature:**

Product is not selfigniting.

· **Explosive properties:**

Product is not explosive. However, formation of explosive air/vapour mixtures are possible.

· **Solvent content:**

· **VOC (EC)**

54.75 %

· **Solids content (weight-%):**

45.3 %

(Contd. on page 7)

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 22.11.2022

Version number 13 (replaces version 12)

Revision: 22.11.2022

Trade name: Rittal Decklack

(Contd. of page 6)

- | | |
|--|------------------------------|
| · Change in condition | |
| · Evaporation rate | Not determined. |
| · Information with regard to physical hazard classes | |
| · Explosives | Void |
| · Flammable gases | Void |
| · Aerosols | Void |
| · Oxidising gases | Void |
| · Gases under pressure | Void |
| · Flammable liquids | Flammable liquid and vapour. |
| · Flammable solids | Void |
| · Self-reactive substances and mixtures | Void |
| · Pyrophoric liquids | Void |
| · Pyrophoric solids | Void |
| · Self-heating substances and mixtures | Void |
| · Substances and mixtures, which emit flammable gases in contact with water | Void |
| · Oxidising liquids | Void |
| · Oxidising solids | Void |
| · Organic peroxides | Void |
| · Corrosive to metals | Void |
| · Desensitised explosives | Void |

SECTION 10: Stability and reactivity

- **10.1 Reactivity** No further relevant information available.
- **10.2 Chemical stability**
- **Thermal decomposition / conditions to be avoided:**
No decomposition if used according to specifications.
- **10.3 Possibility of hazardous reactions** No dangerous reactions known.
- **10.4 Conditions to avoid** No further relevant information available.
- **10.5 Incompatible materials:** No further relevant information available.
- **10.6 Hazardous decomposition products:** Carbon monoxide

SECTION 11: Toxicological information

- **11.1 Information on hazard classes as defined in Regulation (EC) No 1272/2008**
- **Acute toxicity**

- **LD/LC50 values relevant for classification:**

64742-95-6 Hydrocarbons, C9, aromatics

Oral	LD50	>2,000 mg/kg (rat)
Dermal	LD50	>2,000 mg/kg (rabbit)

- **Skin corrosion/irritation** Causes skin irritation.
- **Serious eye damage/irritation** Causes serious eye irritation.
- **Respiratory or skin sensitisation** May cause an allergic skin reaction.
- **STOT-single exposure** May cause respiratory irritation. May cause drowsiness or dizziness.
- **STOT-repeated exposure** May cause damage to organs through prolonged or repeated exposure.

(Contd. on page 8)

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 22.11.2022

Version number 13 (replaces version 12)

Revision: 22.11.2022

Trade name: Rittal Decklack

(Contd. of page 7)

· 11.2 Information on other hazards

· Endocrine disrupting properties

540-97-6	Dodecamethylcyclohexasiloxane	List II
541-02-6	Decamethylcyclopentasiloxane	List II
556-67-2	octamethylcyclotetrasiloxane	List II, III

SECTION 12: Ecological information

- **12.1 Toxicity**
- **Aquatic toxicity:** No further relevant information available.
- **12.2 Persistence and degradability** No further relevant information available.
- **12.3 Bioaccumulative potential** No further relevant information available.
- **12.4 Mobility in soil** No further relevant information available.
- **12.5 Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.
- **12.6 Endocrine disrupting properties**
For information on endocrine disrupting properties see section 11.
- **12.7 Other adverse effects**
- **Remark:** Toxic for fish
- **Additional ecological information:**
- **General notes:**
Water hazard class 2 (German Regulation) : hazardous for water
Do not allow product to reach ground water, water course or sewage system.
Danger to drinking water if even small quantities leak into the ground.
Also poisonous for fish and plankton in water bodies.
Toxic for aquatic organisms

SECTION 13: Disposal considerations

- **13.1 Waste treatment methods**
- **Recommendation**
Must not be disposed together with household garbage. Do not allow product to reach sewage system.
- **Uncleaned packaging:**
- **Recommendation:**
Packagings that may not be cleansed are to be disposed of in the same manner as the product.

SECTION 14: Transport information

- **14.1 UN number or ID number**
- **ADR, IMDG, IATA** UN1263
- **14.2 UN proper shipping name**
- **ADR** UN1263 PAINT, ENVIRONMENTALLY HAZARDOUS

(Contd. on page 9)

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 22.11.2022

Version number 13 (replaces version 12)

Revision: 22.11.2022

Trade name: Rittal Decklack

(Contd. of page 8)

· **IMDG** PAINT (Solvent naphtha, bis-(1,2,2,6,6-penthamethyl-4-piperidyl)sebacate), MARINE POLLUTANT

· **IATA** PAINT

· **14.3 Transport hazard class(es)**

· **ADR**



· **Class** 3 (F1) Flammable liquids.

· **Label** 3

· **IMDG**



· **Class** 3 Flammable liquids.

· **Label** 3

· **IATA**



· **Class** 3 Flammable liquids.

· **Label** 3

· **14.4 Packing group**

· **ADR, IMDG, IATA** III

· **14.5 Environmental hazards:** Product contains environmentally hazardous substances: bis-(1,2,2,6,6-penthamethyl-4-piperidyl)sebacate, Solvent naphtha

· **Marine pollutant:** Symbol (fish and tree)

· **Special marking (ADR):** Symbol (fish and tree)

· **14.6 Special precautions for user** Warning: Flammable liquids.

· **Hazard identification number (Kemler code):** 30

· **EMS Number:** F-E, S-E

· **Stowage Category** A

· **14.7 Maritime transport in bulk according to IMO instruments** Not applicable.

· **Transport/Additional information:**

· **ADR**

· **Limited quantities (LQ)** 5L

· **Transport category** 3

· **Tunnel restriction code** D/E

· **Remarks:** ≤ 5 l: 2.2.3.1.5 ADR

(Contd. on page 10)

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 22.11.2022

Version number 13 (replaces version 12)

Revision: 22.11.2022

Trade name: Rittal Decklack

(Contd. of page 9)

· IMDG	
· Limited quantities (LQ)	5L
· Remarks:	≤ 5 l: 2.2.3.1.5 IMDG
· UN "Model Regulation":	UN 1263 PAINT, 3, III, ENVIRONMENTALLY HAZARDOUS

SECTION 15: Regulatory information

- **15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture**
 - **Directive 2012/18/EU**
 - **Named dangerous substances - ANNEX I** None of the ingredients is listed.
 - **Seveso category**
E2 Hazardous to the Aquatic Environment
P5c FLAMMABLE LIQUIDS
 - **Qualifying quantity (tonnes) for the application of lower-tier requirements** 200 t
 - **Qualifying quantity (tonnes) for the application of upper-tier requirements** 500 t
 - **National regulations:**
 - **Additional classification according to Decree on Hazardous Materials, Annex II:**
- | Class | Share in % |
|-------|------------|
| NK | 50-100 |
- **15.2 Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

SECTION 16: Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

- **Relevant phrases**
- H225 Highly flammable liquid and vapour.
- H226 Flammable liquid and vapour.
- H302 Harmful if swallowed.
- H304 May be fatal if swallowed and enters airways.
- H312 Harmful in contact with skin.
- H315 Causes skin irritation.
- H317 May cause an allergic skin reaction.
- H319 Causes serious eye irritation.
- H332 Harmful if inhaled.
- H335 May cause respiratory irritation.
- H336 May cause drowsiness or dizziness.
- H361d Suspected of damaging the unborn child.
- H361f Suspected of damaging fertility.
- H373 May cause damage to organs through prolonged or repeated exposure.
- H400 Very toxic to aquatic life.
- H410 Very toxic to aquatic life with long lasting effects.
- H411 Toxic to aquatic life with long lasting effects.
- H412 Harmful to aquatic life with long lasting effects.
- EUH066 Repeated exposure may cause skin dryness or cracking.

(Contd. on page 11)

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 22.11.2022

Version number 13 (replaces version 12)

Revision: 22.11.2022

Trade name: Rittal Decklack

(Contd. of page 10)

· **Classification according to Regulation (EC) No 1272/2008**

The classification of the mixture is generally based on the calculation method using substance data according to Regulation (EC) No 1272/2008.

· **Abbreviations and acronyms:**

ADR: Accord relatif au transport international des marchandises dangereuses par route (European Agreement Concerning the International Carriage of Dangerous Goods by Road)

IMDG: International Maritime Code for Dangerous Goods

IATA: International Air Transport Association

GHS: Globally Harmonised System of Classification and Labelling of Chemicals

EINECS: European Inventory of Existing Commercial Chemical Substances

ELINCS: European List of Notified Chemical Substances

CAS: Chemical Abstracts Service (division of the American Chemical Society)

VOC: Volatile Organic Compounds (USA, EU)

LC50: Lethal concentration, 50 percent

LD50: Lethal dose, 50 percent

PBT: Persistent, Bioaccumulative and Toxic

vPvB: very Persistent and very Bioaccumulative

Flam. Liq. 2: Flammable liquids – Category 2

Flam. Liq. 3: Flammable liquids – Category 3

Acute Tox. 4: Acute toxicity – Category 4

Skin Irrit. 2: Skin corrosion/irritation – Category 2

Eye Irrit. 2: Serious eye damage/eye irritation – Category 2

Skin Sens. 1: Skin sensitisation – Category 1

Skin Sens. 1A: Skin sensitisation – Category 1A

Repr. 2: Reproductive toxicity – Category 2

Repr. 2: Reproductive toxicity – Category 2

STOT SE 3: Specific target organ toxicity (single exposure) – Category 3

STOT RE 2: Specific target organ toxicity (repeated exposure) – Category 2

Asp. Tox. 1: Aspiration hazard – Category 1

Aquatic Acute 1: Hazardous to the aquatic environment - acute aquatic hazard – Category 1

Aquatic Chronic 1: Hazardous to the aquatic environment - long-term aquatic hazard – Category 1

Aquatic Chronic 2: Hazardous to the aquatic environment - long-term aquatic hazard – Category 2

Aquatic Chronic 3: Hazardous to the aquatic environment - long-term aquatic hazard – Category 3

· *** Data compared to the previous version altered.**