

Safety data sheet

according to UK REACH

Printing date 13.01.2026

Version number 17 (replaces version 16)

Revision: 13.01.2026

SECTION 1: Identification of the substance/mixture and of the company/undertaking

- **1.1 Product identifier**
- **Trade name:** *Rittal Decklack*
- **1.2 Relevant identified uses of the substance or mixture and uses advised against**
No further relevant information available.
- **Application of the substance / the mixture** Paint
- **1.3 Details of the supplier of the safety data sheet**
- **Manufacturer/Supplier:**
RITTAL GmbH & Co.KG
Auf dem Stützelberg
D-35745 Herborn
Phone: +49 2772 505 0
e-mail: info@rittal.de
- **1.4 Emergency telephone number:**
Informationszentrale gegen Vergiftungen Bonn
Tel.: +49 228/19240 (emergency)
+49 228/287-3-3480 (office)
Fax: +49 228/287-3-3278

SECTION 2: Hazards identification

- **2.1 Classification of the substance or mixture**
- **Classification according to Regulation (EC) No 1272/2008**
 -  GHS02 flame
Flam. Liq. 3 H226 Flammable liquid and vapour.
 -  GHS08 health hazard
STOT RE 2 H373 May cause damage to the hearing organs through prolonged or repeated exposure.
 -  GHS09 environment
Aquatic Chronic 2 H411 Toxic to aquatic life with long lasting effects.
 -  GHS07
Skin Irrit. 2 H315 Causes skin irritation.
Eye Irrit. 2 H319 Causes serious eye irritation.
STOT SE 3 H335-H336 May cause respiratory irritation. May cause drowsiness or dizziness.
- **2.2 Label elements**
- **Labelling according to Regulation (EC) No 1272/2008**
The product is classified and labelled according to the GB CLP regulation.

(Contd. on page 2)

GB

Trade name: Rittal Decklack

(Contd. of page 1)

- **Hazard pictograms** GHS02, GHS07, GHS08, GHS09
- **Signal word** Warning

- **Hazard-determining components of labelling:**

Hydrocarbons, C9, aromatics
 Reaction mass of ethylbenzene and xylene
 2-Methoxy-1-methylethyl acetate

- **Hazard statements**

H226 Flammable liquid and vapour.
 H315 Causes skin irritation.
 H319 Causes serious eye irritation.
 H335-H336 May cause respiratory irritation. May cause drowsiness or dizziness.
 H373 May cause damage to the hearing organs through prolonged or repeated exposure.
 H411 Toxic to aquatic life with long lasting effects.

- **Precautionary statements**

P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
 P260 Do not breathe dust/fume/gas/mist/vapours/spray.
 P280 Wear protective gloves/protective clothing/eye protection/face protection/hearing protection.
 P303+P361+P353 IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water [or shower].
 P304+P340 IF INHALED: Remove person to fresh air and keep comfortable for breathing.
 P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

- **Additional information:**

EUH205 Contains epoxy constituents. May produce an allergic reaction.

- **2.3 Other hazards**

- **Results of PBT and vPvB assessment**

- **PBT:** Not applicable.



- **vPvB:** Not applicable.

SECTION 3: Composition/information on ingredients

- **3.2 Mixtures**

- **Description:** Mixture of substances listed below with nonhazardous additions.

- **Dangerous components:**

CAS: 64742-95-6 EC number: 918-668-5 Reg.nr.: 01-2119455851-35	Hydrocarbons, C9, aromatics 	25-50%
EC number: 905-588-0 Reg.nr.: 01-2119488216-32	Reaction mass of ethylbenzene and xylene 	≥10-<25%
CAS: 108-65-6 EINECS: 203-603-9 Reg.nr.: 01-2119475791-29	2-Methoxy-1-methylethyl acetate 	2.5-<10%
CAS: 112-07-2 EINECS: 203-933-3 Reg.nr.: 01-2119475112-47	2-Butoxyethyl acetate 	1-<2.5%

(Contd. on page 3)

GB

Safety data sheet

according to UK REACH

Printing date 13.01.2026

Version number 17 (replaces version 16)

Revision: 13.01.2026

Trade name: Rittal Decklack

(Contd. of page 2)

CAS: 108-88-3 EINECS: 203-625-9 Reg.nr.: 01-2119471310-51	Toluene Flam. Liq. 2, H225; Repr. 2, H361d; STOT RE 2, H373; Asp. Tox. 1, H304; Skin Irrit. 2, H315; STOT SE 3, H336	<1%
CAS: 1675-54-3 EINECS: 216-823-5 Reg.nr.: 01-2119456619-26	Bis[4-(2,3-epoxypropoxy)phenyl]propane Aquatic Chronic 2, H411; Skin Irrit. 2, H315; Eye Irrit. 2, H319; Skin Sens. 1, H317, EUH205 Specific concentration limits: Eye Irrit. 2; H319: C ≥ 5 % Skin Irrit. 2; H315: C ≥ 5 %	≥0.25-<1%

· Additional information: For the wording of the listed hazard phrases refer to section 16.

SECTION 4: First aid measures

- 4.1 Description of first aid measures
- General information: Immediately remove any clothing soiled by the product.
- After inhalation: Supply fresh air; consult doctor in case of complaints.
- After skin contact: Immediately rinse with water.
- After eye contact: Rinse opened eye for several minutes under running water. If symptoms persist, consult a doctor.
- After swallowing: If symptoms persist consult doctor.
- 4.2 Most important symptoms and effects, both acute and delayed
- No further relevant information available.
- 4.3 Indication of any immediate medical attention and special treatment needed
- No further relevant information available.

SECTION 5: Firefighting measures

- 5.1 Extinguishing media
- Suitable extinguishing agents: CO₂, powder or water spray. Fight larger fires with water spray or alcohol resistant foam.
- For safety reasons unsuitable extinguishing agents: Water with full jet
- 5.2 Special hazards arising from the substance or mixture
- During heating or in case of fire poisonous gases are produced.
- 5.3 Advice for firefighters
- Protective equipment: Mouth respiratory protective device.

SECTION 6: Accidental release measures

- 6.1 Personal precautions, protective equipment and emergency procedures
- Mount respiratory protective device.
- Wear protective equipment. Keep unprotected persons away.
- 6.2 Environmental precautions:
- Do not allow product to reach sewage system or any water course.
- Inform respective authorities in case of seepage into water course or sewage system.
- Do not allow to enter sewers/ surface or ground water.
- 6.3 Methods and material for containment and cleaning up:
- Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders, sawdust).
- Dispose contaminated material as waste according to section 13.

(Contd. on page 4)

GB

Trade name: Rittal Decklack

Ensure adequate ventilation.

(Contd. of page 3)

6.4 Reference to other sections

See Section 7 for information on safe handling.

See Section 8 for information on personal protection equipment.

See Section 13 for disposal information.

SECTION 7: Handling and storage
7.1 Precautions for safe handling

Ensure good ventilation/exhaustion at the workplace.

Prevent formation of aerosols.

Information about fire - and explosion protection:

Keep ignition sources away - Do not smoke.

Protect against electrostatic charges.

Keep respiratory protective device available.

7.2 Conditions for safe storage, including any incompatibilities
Storage:

Requirements to be met by storerooms and receptacles: No special requirements.

Information about storage in one common storage facility: Store away from foodstuffs.

Further information about storage conditions: Keep container tightly sealed.

Storage class: 3

7.3 Specific end use(s) No further relevant information available.

SECTION 8: Exposure controls/personal protection
8.1 Control parameters
Ingredients with limit values that require monitoring at the workplace:
108-65-6 2-Methoxy-1-methylethyl acetate

WEL	Short-term value: 548 mg/m ³ , 100 ppm Long-term value: 274 mg/m ³ , 50 ppm Sk
-----	--

112-07-2 2-Butoxyethyl acetate

WEL	Short-term value: 332 mg/m ³ , 50 ppm Long-term value: 133 mg/m ³ , 20 ppm Sk
-----	---

108-88-3 Toluene

WEL	Short-term value: 384 mg/m ³ , 100 ppm Long-term value: 191 mg/m ³ , 50 ppm Sk
-----	--

DNELs
Reaction mass of ethylbenzene and xylene

Dermal	DNEL	212 mg/kg (Arbeiter)
Inhalative	DNEL	221 mg/m ³ (Arbeiter)

112-07-2 2-Butoxyethyl acetate

Dermal	DNEL	169 mg/kg (Arbeiter)
Inhalative	DNEL	133 mg/m ³ (Arbeiter)

(Contd. on page 5)

GB

Safety data sheet

according to UK REACH

Printing date 13.01.2026

Version number 17 (replaces version 16)

Revision: 13.01.2026

Trade name: Rittal Decklack

(Contd. of page 4)

- **Additional information:** The lists valid during the making were used as basis.

- **8.2 Exposure controls**

- **Appropriate engineering controls** No further data; see section 7.

- **Individual protection measures, such as personal protective equipment**

- **General protective and hygienic measures:**

Keep away from foodstuffs, beverages and feed.

Immediately remove all soiled and contaminated clothing

Wash hands before breaks and at the end of work.

Store protective clothing separately.

Avoid contact with the eyes.

Avoid contact with the eyes and skin.

- **Respiratory protection:**



In case of brief exposure or low pollution use respiratory filter device. In case of intensive or longer exposure use self-contained respiratory protective device.

- **Hand protection**

Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation



Protective gloves (EN 374)

The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.

- **Material of gloves**

The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked prior to the application.

- **Breakthrough time of glove material**

The exact break trough time has to be found out by the manufacturer of the protective gloves and has to be observed.

- **Eye/face protection**



Tightly sealed goggles

* SECTION 9: Physical and chemical properties

- **9.1 Information on basic physical and chemical properties**

- **General Information**

- **Physical state**

Liquid

- **Colour:**

According to product specification

- **Odour:**

Characteristic

- **Odour threshold:**

Not determined.

(Contd. on page 6)

GB

Trade name: Rittal Decklack

(Contd. of page 5)

· Melting point/freezing point:	Undetermined.
· Boiling point or initial boiling point and boiling range	136 °C (Reaction mass of ethylbenzene and xylene) Flammable.
· Flammability	
· Lower and upper explosion limit	
· Lower:	0.6 Vol % (64742-95-6 Hydrocarbons, C9, aromatics)
· Upper:	7.5 Vol % (64742-95-6 Hydrocarbons, C9, aromatics)
· Flash point:	24 °C (DIN EN ISO 1523:2002)
· Auto-ignition temperature:	>400 °C (DIN 51794, 64742-95-6 Hydrocarbons, C9, aromatics)
· Decomposition temperature:	Not determined.
· pH	Not determined.
· Viscosity:	
· Kinematic viscosity at 20 °C	160-180 s (DIN 53211/4)
· Dynamic:	Not determined.
· Solubility	
· water:	Not miscible or difficult to mix.
· Partition coefficient n-octanol/water (log value)	Not determined.
· Vapour pressure at 20 °C:	10 hPa (Reaction mass of ethylbenzene and xylene)
· Density and/or relative density	
· Density at 20 °C:	1.037 g/cm³ (DIN EN ISO 2811-1)
· Relative density	Not determined.
· Vapour density	Not determined.
· 9.2 Other information	
· Appearance:	
· Form:	Fluid
· Important information on protection of health and environment, and on safety.	
· Ignition temperature:	Product is not selfigniting.
· Explosive properties:	Product is not explosive. However, formation of explosive air/vapour mixtures are possible.
· Solvent content:	
· VOC (EC)	55.37 %
· Solids content (weight-%):	44.3 %
· Change in condition	
· Evaporation rate	Not determined.
· Information with regard to physical hazard classes	
· Explosives	Void
· Flammable gases	Void
· Aerosols	Void
· Oxidising gases	Void
· Gases under pressure	Void
· Flammable liquids	Flammable liquid and vapour.
· Flammable solids	Void

(Contd. on page 7)

GB

Safety data sheet

according to UK REACH

Printing date 13.01.2026

Version number 17 (replaces version 16)

Revision: 13.01.2026

Trade name: Rittal Decklack

(Contd. of page 6)

· Self-reactive substances and mixtures	Void
· Pyrophoric liquids	Void
· Pyrophoric solids	Void
· Self-heating substances and mixtures	Void
· Substances and mixtures, which emit flammable gases in contact with water	Void
· Oxidising liquids	Void
· Oxidising solids	Void
· Organic peroxides	Void
· Corrosive to metals	Void
· Desensitised explosives	Void

* SECTION 10: Stability and reactivity

- **10.1 Reactivity** No further relevant information available.
- **10.2 Chemical stability**
- **Thermal decomposition / conditions to be avoided:**
No decomposition if used according to specifications.
- **10.3 Possibility of hazardous reactions** No dangerous reactions known.
- **10.4 Conditions to avoid** No further relevant information available.
- **10.5 Incompatible materials:** No further relevant information available.
- **10.6 Hazardous decomposition products:**
Possible in traces.
Nitrogen oxides
Hydrogen chloride (HCl)
Carbon monoxide
Nitrogen oxides (NOx)

* SECTION 11: Toxicological information

- **11.1 Information on hazard classes as defined in Regulation (EC) No 1272/2008**
- **Acute toxicity** Based on available data, the classification criteria are not met.

· **LD/LC50 values relevant for classification:**

64742-95-6 Hydrocarbons, C9, aromatics

Oral	LD50	>2,000 mg/kg (rat)
Dermal	LD50	>2,000 mg/kg (rabbit)

Reaction mass of ethylbenzene and xylene

Oral	LD50	3,500 mg/kg (rat)
Dermal	LD50	15,400 mg/kg (rat)
Inhalative	LC50/4 h	17.6 mg/l (rat)

108-65-6 2-Methoxy-1-methylethyl acetate

Oral	LD50	8,532 mg/kg (rat)
------	------	-------------------

112-07-2 2-Butoxyethyl acetate

Oral	LD50	1,880 mg/kg (rat)
Dermal	LD50	1,480 mg/kg (rabbit)

(Contd. on page 8)

GB

Safety data sheet

according to UK REACH

Printing date 13.01.2026

Version number 17 (replaces version 16)

Revision: 13.01.2026

Trade name: Rittal Decklack

(Contd. of page 7)

108-88-3 Toluene

Oral	LD50	>5,300 mg/kg (rat)
Dermal	LD50	12,124 mg/kg (rabbit)
Inhalative	LC50/4 h	28.1 mg/l (rat)

- **Primary irritant effect:**
- **Skin corrosion/irritation** Causes skin irritation.
- **Serious eye damage/irritation** Causes serious eye irritation.
- **STOT-single exposure** May cause respiratory irritation. May cause drowsiness or dizziness.
- **STOT-repeated exposure**
May cause damage to the hearing organs through prolonged or repeated exposure.
- **11.2 Information on other hazards**

- **Endocrine disrupting properties**

None of the ingredients is listed.

SECTION 12: Ecological information

- **12.1 Toxicity**
- **Aquatic toxicity:** No further relevant information available.
- **12.2 Persistence and degradability** No further relevant information available.
- **12.3 Bioaccumulative potential** No further relevant information available.
- **12.4 Mobility in soil** No further relevant information available.
- **12.5 Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.
- **12.6 Endocrine disrupting properties**
For information on endocrine disrupting properties see section 11.
- **12.7 Other adverse effects**
- **Remark:** Toxic for fish
- **Additional ecological information:**
- **General notes:**
Water hazard class 2 (German Regulation) : hazardous for water
Do not allow product to reach ground water, water course or sewage system.
Danger to drinking water if even small quantities leak into the ground.
Also poisonous for fish and plankton in water bodies.
Toxic for aquatic organisms

SECTION 13: Disposal considerations

- **13.1 Waste treatment methods**
- **Recommendation**
Must not be disposed together with household garbage. Do not allow product to reach sewage system.
- **Uncleaned packaging:**
- **Recommendation:**
Packagings that may not be cleansed are to be disposed of in the same manner as the product.

GB

(Contd. on page 9)

Trade name: Rittal Decklack

(Contd. of page 8)

SECTION 14: Transport information

· 14.1 UN number or ID number	
· ADR, IMDG, IATA	UN1263
· 14.2 UN proper shipping name	
· ADR	UN1263 PAINT, ENVIRONMENTALLY HAZARDOUS
· IMDG	PAINT (Solvent naphtha), MARINE POLLUTANT
· IATA	PAINT
· 14.3 Transport hazard class(es)	
· ADR	 
· Class	3 (F1) Flammable liquids.
· Label	3
· IMDG	 
· Class	3 Flammable liquids.
· Label	3
· IATA	
· Class	3 Flammable liquids.
· Label	3
· 14.4 Packing group	
· ADR, IMDG, IATA	III
· 14.5 Environmental hazards:	Product contains environmentally hazardous substances: Solvent naphtha
· Marine pollutant:	Symbol (fish and tree)
· Special marking (ADR):	Symbol (fish and tree)
· 14.6 Special precautions for user	Warning: Flammable liquids.
· Hazard identification number (Kemler code):	30
· EMS Number:	F-E, S-E
· Stowage Category	A
· 14.7 Maritime transport in bulk according to IMO instruments	Not applicable.

(Contd. on page 10)

GB

Trade name: Rittal Decklack

(Contd. of page 9)

· Transport/Additional information:
· ADR
· Limited quantities (LQ)

5L

· Transport category

3

· Tunnel restriction code

D/E

· Remarks:
 ≤ 5 l: 2.2.3.1.5 ADR
· IMDG
· Limited quantities (LQ)

5L

· Remarks:
 ≤ 5 l: 2.3.2.5 IMDG
· UN "Model Regulation":

UN 1263 PAINT, 3, III, ENVIRONMENTALLY HAZARDOUS

*** SECTION 15: Regulatory information**
· 15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture
· Poisons Act
· Regulated explosives precursors

None of the ingredients is listed.

· Regulated poisons

None of the ingredients is listed.

· Reportable explosives precursors

None of the ingredients is listed.

· Reportable poisons

None of the ingredients is listed.

· Directive 2012/18/EU
· Named dangerous substances - ANNEX I None of the ingredients is listed.

· Seveso category

E2 Hazardous to the Aquatic Environment

P5c FLAMMABLE LIQUIDS

· Qualifying quantity (tonnes) for the application of lower-tier requirements 200 t

· Qualifying quantity (tonnes) for the application of upper-tier requirements 500 t

· National regulations:
· Additional classification according to Decree on Hazardous Materials, Annex II:

Class	Share in %
I	<1
NK	50-100

· 15.2 Chemical safety assessment: A Chemical Safety Assessment has not been carried out.

*** SECTION 16: Other information**

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

(Contd. on page 11)

GB

Trade name: Rittal Decklack

(Contd. of page 10)

· Relevant phrases

- H225 Highly flammable liquid and vapour.
- H226 Flammable liquid and vapour.
- H302 Harmful if swallowed.
- H304 May be fatal if swallowed and enters airways.
- H312 Harmful in contact with skin.
- H315 Causes skin irritation.
- H317 May cause an allergic skin reaction.
- H319 Causes serious eye irritation.
- H332 Harmful if inhaled.
- H335 May cause respiratory irritation.
- H336 May cause drowsiness or dizziness.
- H361d Suspected of damaging the unborn child.
- H373 May cause damage to organs through prolonged or repeated exposure.
- H411 Toxic to aquatic life with long lasting effects.
- H412 Harmful to aquatic life with long lasting effects.
- EUH066 Repeated exposure may cause skin dryness or cracking.
- EUH205 Contains epoxy constituents. May produce an allergic reaction.

· Classification according to Regulation (EC) No 1272/2008

The classification of the mixture is generally based on the calculation method using substance data according to Regulation (EC) No 1272/2008.

· Abbreviations and acronyms:

- ADR: Accord relatif au transport international des marchandises dangereuses par route (European Agreement Concerning the International Carriage of Dangerous Goods by Road)
- IMDG: International Maritime Code for Dangerous Goods
- IATA: International Air Transport Association
- GHS: Globally Harmonised System of Classification and Labelling of Chemicals
- EINECS: European Inventory of Existing Commercial Chemical Substances
- ELINCS: European List of Notified Chemical Substances
- CAS: Chemical Abstracts Service (division of the American Chemical Society)
- VOC: Volatile Organic Compounds (USA, EU)
- DNEL: Derived No-Effect Level (UK REACH)
- LC50: Lethal concentration, 50 percent
- LD50: Lethal dose, 50 percent
- PBT: Persistent, Bioaccumulative and Toxic
- vPvB: very Persistent and very Bioaccumulative
- Flam. Liq. 2: Flammable liquids – Category 2
- Flam. Liq. 3: Flammable liquids – Category 3
- Acute Tox. 4: Acute toxicity – Category 4
- Skin Irrit. 2: Skin corrosion/irritation – Category 2
- Eye Irrit. 2: Serious eye damage/eye irritation – Category 2
- Skin Sens. 1: Skin sensitisation – Category 1
- Repr. 2: Reproductive toxicity – Category 2
- STOT SE 3: Specific target organ toxicity (single exposure) – Category 3
- STOT RE 2: Specific target organ toxicity (repeated exposure) – Category 2
- Asp. Tox. 1: Aspiration hazard – Category 1
- Aquatic Chronic 2: Hazardous to the aquatic environment - long-term aquatic hazard – Category 2
- Aquatic Chronic 3: Hazardous to the aquatic environment - long-term aquatic hazard – Category 3

· * Data compared to the previous version altered.