



### Kompakt-Schaltschränke AE

Edelstahl Handbuch 33, Seite 184


AE 1001.X00 – AE 1016.X00




- 1** Bei AE 1001.X00, AE 1002.X00, AE 1003.X00, AE 1004.X00, AE 1005.X00, AE 1006.X00, AE 1009.X00, AE 1011.X00 nur ein Vorreiber in der Mitte und ohne mittigen Bolzen
- 2** 50 bei AE 1001.X00, AE 1002.X00
- 3** Entfallen bei AE 1001.X00, AE 1002.X00




Montageplatten  
AE 1001.X00,  
AE 1002.X00




AE 1003.X00 – AE 1016.X00




AE 1017.X00




AE 1018.X00 (AE 1019.X00)




- 1** Vorreiber bei AE 1018.X00
- 2** Stangenverschluss bei AE 1019.X00



Montageplatten  
AE 1018.X00



AE 1017.X00 (AE 1019.X00)



Maße in Klammern für AE 1019.X00.

| Best.-Nr. AE    | Breitenmaße mm |     |     |    | Höhenmaße mm |     |     |     | Tiefenmaße mm |           | Montageplatten mm |     |     |     | Materialstärke mm |     |               |
|-----------------|----------------|-----|-----|----|--------------|-----|-----|-----|---------------|-----------|-------------------|-----|-----|-----|-------------------|-----|---------------|
| Edelstahl       | B1             | B2  | B3  | B4 | H1           | H2  | H3  | H4  | T1            | T2        | F1                | F2  | G1  | G2  | Gehäuse           | Tür | Montageplatte |
| <b>1001.X00</b> | 200            | 167 | –   | 56 | 300          | 295 | 274 | 225 | 122           | 100       | –                 | –   | –   | –   | 1,25              | 1,5 | 2,0           |
| <b>1002.X00</b> | 200            | 167 | –   | 56 | 300          | 295 | 274 | 225 | 157           | 135       | –                 | –   | –   | –   | 1,25              | 1,5 | 2,0           |
| <b>1003.X00</b> | 300            | 260 | 175 | 66 | 300          | 295 | 260 | 225 | 212           | 168 – 184 | 254               | 215 | 275 | 250 | 1,38              | 1,5 | 2,0           |
| <b>1004.X00</b> | 380            | 340 | 250 | 66 | 300          | 295 | 260 | 225 | 157           | 113 – 129 | 334               | 295 | 275 | 250 | 1,38              | 1,5 | 2,0           |
| <b>1011.X00</b> | 380            | 340 | 250 | 66 | 300          | 295 | 260 | 225 | 212           | 168 – 184 | 334               | 295 | 275 | 250 | 1,38              | 1,5 | 2,0           |
| <b>1005.X00</b> | 300            | 260 | 175 | 66 | 380          | 375 | 340 | 275 | 212           | 168 – 184 | 334               | 295 | 275 | 250 | 1,38              | 1,5 | 2,0           |
| <b>1006.X00</b> | 380            | 340 | 250 | 66 | 380          | 375 | 340 | 275 | 212           | 168 – 184 | 334               | 295 | 355 | 330 | 1,38              | 1,5 | 2,0           |
| <b>1015.X00</b> | 400            | 360 | 275 | 66 | 500          | 495 | 460 | 425 | 212           | 168 – 184 | 354               | 315 | 475 | 450 | 1,38              | 1,5 | 2,0           |
| <b>1007.X00</b> | 500            | 460 | 375 | 66 | 500          | 495 | 460 | 425 | 212           | 168 – 184 | 449               | 410 | 470 | 445 | 1,38              | 2,0 | 2,5           |
| <b>1013.X00</b> | 500            | 460 | 375 | 66 | 500          | 495 | 460 | 425 | 302           | 258 – 274 | 449               | 410 | 470 | 445 | 1,50              | 2,0 | 2,5           |
| <b>1008.X00</b> | 380            | 340 | 250 | 66 | 600          | 595 | 560 | 525 | 212           | 168 – 184 | 334               | 295 | 570 | 545 | 1,38              | 1,5 | 2,5           |
| <b>1009.X00</b> | 600            | 560 | 475 | 66 | 380          | 375 | 340 | 275 | 212           | 168 – 184 | 549               | 510 | 355 | 330 | 1,38              | 1,5 | 2,5           |
| <b>1010.X00</b> | 600            | 560 | 475 | 66 | 600          | 595 | 560 | 525 | 212           | 168 – 184 | 549               | 510 | 570 | 545 | 1,38              | 2,0 | 2,5           |
| <b>1012.X00</b> | 600            | 560 | 475 | 66 | 760          | 755 | 720 | 675 | 212           | 168 – 184 | 549               | 510 | 730 | 705 | 1,38              | 2,0 | 3,0           |
| <b>1014.X00</b> | 760            | 720 | 625 | 66 | 760          | 755 | 720 | 675 | 302           | 258 – 274 | 704               | 665 | 730 | 705 | 1,50              | 2,0 | 3,0           |
| <b>1016.X00</b> | 800            | 760 | 675 | 66 | 1000         | 955 | 960 | 925 | 302           | 258 – 274 | 739               | 700 | 955 | 930 | 1,50              | 2,0 | 3,0           |
| <b>1017.X00</b> | 800            | –   | –   | –  | 1200         | –   | –   | –   | 302           | –         | –                 | –   | –   | –   | 1,50              | 2,0 | 3,0           |
| <b>1018.X00</b> | 1000           | –   | –   | –  | 1000         | –   | –   | –   | 302           | –         | 939               | 900 | 955 | 930 | 1,50              | 2,0 | 3,0           |
| <b>1019.X00</b> | 1000           | –   | –   | –  | 1200         | –   | –   | –   | 302           | –         | –                 | –   | –   | –   | 1,50              | 2,0 | 3,0           |