


# IT infrastructure

## IT rack systems


### Network/server racks VX IT

with glazed door, with 482.6 mm (19") mounting angles, standard, W 600 x D 600 mm


Front view




Side view




Rear view




Section A - A



Section B - B




Bottom view




### Network/server racks VX IT

with glazed door, with 482.6 mm (19") mounting angles, standard, W 600 x D 600 mm

Front view without doors



Top view



- B1 = Overall width without side panels
- B2 = Width of front door
- B3 = Clearance of enclosure frame
- B4 = Clearance base opening (footprint of frame excluding levelling feet, inner edge)
- B5 = Mounting dimension 19"
- B6 = Clearance within the 482.6 mm (19") mounting level
- B7 = Footprint of levelling feet (attached to the base frame)
- B8 = Footprint of levelling feet (attached to the frame corner pieces)
- B9 = Footprint of frame excluding levelling feet, outer edge
- B10 = Width of brush strip
- H1 = Overall height
- H3 = Clearance of enclosure frame
- T1 = Overall depth without handles
- T2 = Overall depth with handles
- T3 = Clearance of enclosure frame
- T4 = Clearance base opening
- T6 = Clearance in front of 482.6 mm (19") mounting level
- T7 = Clearance behind 482.6 mm (19") mounting level
- T8 = Distance between frame and 482.6 mm (19") mounting level, rear
- T9 = Footprint of levelling feet (attached to the base frame)
- T10 = Footprint of levelling feet (attached to the frame corner pieces)
- T11 = Depth of brush strip

- 1 5325.121, 5326.121, 5326.131, 5329.131 one-piece rear door  
5325.121, 5326.121, 5326.131 two hinges,  
5329.131 four hinges
- 2 Cut-out for fan mounting plate 5502.010,  
not applicable to 5326.131, 5329.131
- 3 5326.131, 5329.131 roof plate, one-piece, solid
- 4 5326.131, 5329.131 base tray with gland plate,  
multi-piece, solid

**Note:**

- With fitted side panels, the overall width B1 is increased by 9 mm
- Depending on the baying connector, the distance between bayed enclosures is either 1 or 3 mm

Model no. DK	U	Width dimensions mm										Height dimensions mm		Depth dimensions mm										
		B1	B2	B3	B4	B5	B6	B7	B8	B9	B10	H1	H3	T1	T2	T3	T4	T6 <sup>1)</sup>	T7 <sup>2)</sup>	T8	T9	T10	T11	
5325.121	15	599	593	511	452	465	451	475	535	551	450	817.5	711	625	710	511	452	150	449	405	475	535	125	
5326.121	24	599	593	511	452	465	451	475	535	551	450	1217.5	1111	625	710	511	452	150	449	405	475	535	125	
5326.131	24	599	593	511	452	465	451	475	535	551	-	1217.5	1111	625	710	511	452	150	449	405	475	535	-	
5327.121	38	599	593	511	452	465	451	475	535	551	450	1817.5	1711	625	710	511	452	150	449	405	475	535	125	
5329.111	42	599	593	511	452	465	451	475	535	551	450	2017.5	1911	625	710	511	452	150	449	405	475	535	125	
5329.121	42	599	593	511	452	465	451	475	535	551	450	2017.5	1911	625	710	511	452	150	449	405	475	535	125	
5329.131	42	599	593	511	452	465	451	475	535	551	-	2017.5	1911	625	710	511	452	150	449	405	475	535	-	

<sup>1)</sup> Min. distance 37.5 mm <sup>2)</sup> Max. distance 561.5 mm