

Rittal – The System.

Faster – better – everywhere.

LED system light – SZ 2500.211

Date : Sep 27, 2020

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



LED system light – SZ 2500.211

created: 27.09.2020 build on www.rittal.com/in-en



Product description

Design: with socket

Benefits: Optimum illumination of the entire enclosure
Optionally with clip, screw and magnetic attachment
A configuration to suit every application

Equipment: Socket
90° rotating connector
Adjustable light distribution

Material: Light body: Extruded aluminium
Light cover: Polycarbonate (halogen-free)
Light ends: PC-ABS (halogen-free)

Colour: Enclosure: RAL 7016

**Protection category
IP to IEC 60 529:** IP 20

Supply includes: Assembly screws

Product features

Dimensions: Width: 437 mm
Height: 80 mm
Depth: 44 mm

**Rated operating
voltage:** 100 V - 240 V, 1~, 50 Hz/60 Hz

Installation options: Directly onto the enclosure section with 25 mm pitch pattern

Operating temperature:	Operation (environment): -20 °C...+55 °C
Power consumption:	11 W
Equipment (electrical):	Jack/socket (type): GB (type G, BS 1363)
Rated insulation voltage:	300 V AC
Rated impulse withstand voltage, phase to earth:	2500 V AC
Luminous flux:	900 lm
Light colour:	4000 K (neutral white)
Protection class:	II (all-insulated)
Overvoltage category:	II
Connection options:	Infeed, 3-pole Through-wiring, 3-pole Door-operated switch
Light – installation type:	Screw-fastening Clip attachment
Packs of:	1 pc(s).
Weight/pack:	0.61 kg
Copper weight (kg per piece):	0
EAN:	4028177811355
Customs tariff number:	94054099
ETIM 7.0:	EC000321
ETIM 6.0:	EC000321
eCl@ss 8.0/8.1:	27189241
eCl@ss 6.0/6.1:	27189241
Product description:	SZ System Light LED, 900 Lumen, L: 437 mm, 100-240 V, with earthing-pin socket for Great Britain

Approvals

Approvals:	CCC ENEC
-------------------	-------------

Certificates:	EAC
----------------------	-----

Declarations:	Declaration of conformity
----------------------	---------------------------